


RM3006



Encoder multiturn absolut dengan poros solid

RMS0025-E24/E



1 M4 kedalaman 6 mm



Karakteristik produk

Resolusi	8192 langkah; 4096 putaran; 25 bit
Interface komunikasi	PROFIBUS DP
Desain poros	poros solid
Diameter poros [mm]	6

Aplikasi

Prinsip fungsi	absolut
Tipe putaran	multiturn

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	100; ((24 V))
Pelindung polaritas terbalik	ya

Output

Kode	binari
------	--------

Rentang pengukuran/pengaturan

Resolusi	8192 langkah; 4096 putaran; 25 bit
----------	------------------------------------

Software/pemrograman

Opsi pengaturan parameter	arah penghitungan nilai kode; Resolusi; titik nol; switch batas HI dan LO; indikator gerakan; multiturn/singleturn
Fungsi diagnostik	alarm; peringatan; status; nomor seri encoder



Encoder multiturn absolut dengan poros solid

RMS0025-E24/E

Alamat	switch pemilih alamat; 0...126	
Interface		
Interface komunikasi	PROFIBUS DP	
PROFIBUS DP		
Standar transmisi	DPV2	
Kondisi pengoperasian		
Suhu sekitar	[°C]	-40...85
Kelembapan udara relatif maks.	[%]	98
Perlindungan	IP 67; (pada casing: IP 67; pada poros: IP 67)	
Pengujian/persetujuan		
Tahan guncangan		100 g (6 ms)
Ketahanan terhadap getaran		10 g (10...2000 Hz)
MTTF	[ANN]	13.5
Data teknis		
Berat	[g]	611
Dimensi	[mm]	Ø 58 / L = 94
Material		aluminium
Putaran maks., mekanis	[U/min]	12000
Desain poros		poros solid
Diameter poros	[mm]	6
Material poros		baja (1.4104)
Beban poros aksial maks. (di ujung poros)	[N]	40
Beban poros radial maks. (di ujung poros)	[N]	110
Flensa pemasangan		flensa sinkronisasi
Koneksi listrik		
strip terminal pada ruang terminal:		