


RM7013

Encoder multiturn absolut dengan poros solid

RMK0025-H24/E



- | | |
|---|-------------------|
| 1 | M3 kedalaman 6 mm |
| 2 | M4 kedalaman 6 mm |



Karakteristik produk

Resolusi	8192 langkah; 4096 putaran; 25 bit
Interface komunikasi	DeviceNet
Desain poros	poros solid
Diameter poros [mm]	10

Aplikasi

Prinsip fungsi	absolut
Tipe putaran	multiturn

Data kelistrikan

Tegangan pengoperasian	[V]	10...30 DC
Konsumsi arus	[mA]	230; ((10 V DC); 100 (24 V DC))
Pelindung polaritas terbalik		ya

Output

Pelindung hubung singkat	ya
Kode	binari

Rentang pengukuran/pengaturan

Resolusi	8192 langkah; 4096 putaran; 25 bit
----------	------------------------------------



Encoder multiturn absolut dengan poros solid

RMK0025-H24/E

Software/pemrograman		
Opsi pengaturan parameter	resolusi per putaran; resolusi total; arah putaran; nilai preset; Tipe operasi; MAC ID; Baud rate	
Alamat	switch pemilih alamat; 0...99; resistor pemutus	
Interface		
Interface komunikasi	DeviceNet	
DeviceNet		
Protokol	CIP (Common Industrial Protocol)	
Kondisi pengoperasian		
Suhu sekitar	[°C]	-40...85
Kelembapan udara relatif maks.	[%]	98
Perlindungan	IP 67	
Pengujian/persetujuan		
Tahan guncangan		100 g (6 ms)
Ketahanan terhadap getaran		10 g (10...1000 Hz)
MTTF	[ANN]	13
Data teknis		
Berat	[g]	592
Dimensi	[mm]	Ø 58 / L = 110
Material	penutup casing: aluminium; casing: baja	
Putaran maks., mekanis	[U/min]	12000
Desain poros	poros solid	
Diameter poros	[mm]	10
Material poros	baja tahan karat (1.4305/303)	
Beban poros aksial maks. (di ujung poros)	[N]	40
Beban poros radial maks. (di ujung poros)	[N]	110
Flensa pemasangan	flensa penjepit	
Koneksi listrik		
strip terminal pada ruang terminal:		