




- 1 M3 kedalaman 6 mm
- 2 M4 kedalaman 6 mm



Karakteristik produk

Resolusi	8192 langkah; 13 bit
Interface komunikasi	CAN
Desain poros	poros solid
Diameter poros [mm]	10

Aplikasi

Prinsip fungsi	absolut
Tipe putaran	singleturn

Data kelistrikan

Tegangan pengoperasian	[V]	10...30 DC
Konsumsi arus	[mA]	100; ((10 V DC); 60 (24 V DC))
Pelindung polaritas terbalik		ya

Output

Kode	binari
------	--------

Rentang pengukuran/pengaturan

Resolusi	8192 langkah; 13 bit
----------	----------------------

Software/pemrograman

Opsi pengaturan parameter	Parameter CAN; penskalaan; preset; Baud rate; arah putaran; Node ID
Alamat	switch pemilih alamat; 0...126



Encoder singleturn absolut dengan poros solid

RMK0013-C24/E

Interface		
Interface komunikasi	CAN	
Pengaturan pabrik	Baud rate: 125 kBit/s	
	ID node: 32	
CAN		
Protokol	CANopen; DSP - 406 V3.1; DS 301 V4.02; DS 306 V2.0	
Pengaturan pabrik	Baud rate: 125 kBit/s	
	ID node: 32	
Kondisi pengoperasian		
Suhu sekitar	[°C]	-40...85
Kelembapan udara relatif maks.	[%]	98
Perlindungan	IP 65; (pada casing: IP 65; pada poros: IP 64)	
Pengujian/persetujuan		
Tahan guncangan		100 g (6 ms)
Ketahanan terhadap getaran		10 g (10...1000 Hz)
MTTF	[ANN]	13
Data teknis		
Berat	[g]	555
Dimensi	[mm]	Ø 58 / L = 99
Material		aluminium
Putaran maks., mekanis	[U/min]	12000
Desain poros		poros solid
Diameter poros	[mm]	10
Material poros		baja (1.4104)
Beban poros aksial maks. (di ujung poros)	[N]	40
Beban poros radial maks. (di ujung poros)	[N]	110
Flensa pemasangan		flensa penjepit
Elemen display/pengoperasian		
Display	Preoperational Mode	LED, hijau berkedip
	Operational Mode	LED, hijau
	pesan kesalahan	LED, merah berkedip
Koneksi listrik		
strip terminal pada ruang terminal:		