


Encoder poros solid

RS-0500-I24/NB

Produk tidak tersedia - entri arsip



- 1 tanda referensi
2 M3 kedalaman 10 mm



Karakteristik produk

Resolusi	500 resolusi
Desain poros	poros solid
Diameter poros [mm]	6

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	150

Output

Desain kelistrikan	HTL
Beban arus maks. per output [mA]	50
Frekuensi peralihan [kHz]	50
Tipe pelindung hubung singkat	< 60 s
Perbedaan fase A dan B [°]	90

Rentang pengukuran/pengaturan

Resolusi	500 resolusi
----------	--------------

Kondisi pengoperasian

Suhu sekitar [°C]	-20...70
Suhu penyimpanan [°C]	-30...80
Kelembapan udara relatif maks. [%]	98
Perlindungan	IP 64



Encoder poros solid

RS-0500-I24/NB

Pengujian/persetujuan

Tahan guncangan	30 g (6 ms)
Ketahanan terhadap getaran	10 g (55...2000 Hz)

Data teknis


Dimensi [mm]	Ø 40 / L = 83
Material	aluminium
Putaran maks., mekanis [U/min]	10000
Torsi awal maks. [Nm]	1
Torsi suhu referensi [°C]	20
Desain poros	poros solid
Diameter poros [mm]	6
Material poros	baja tahan karat
Beban poros aksial maks. (di ujung poros) [N]	20
Beban poros radial maks. (di ujung poros) [N]	20

Koneksi listrik

Kabel: 0.4 m; radial

putih	A
hijau	B
kuning	indeks 0
coklat	10...30V (Up)
abu-abu	0V (Un)
penutup	casing

Diagram dan grafik

Diagram pulsa	 Output A Output B indeks 0
---------------	--