


RU-0250-I05/N2

Technical drawing of a circular part with a 120° sector removed. The part has an outer diameter of 42. A section line A-A is shown at a 30° angle. Callout 1 points to the outer edge, and callout 2 points to the inner edge of the sector.



CE



Encoder inkremental dengan poros solid

RU-0250-I05/N2

Ketahanan terhadap getaran	10 g (55...2000 Hz)
----------------------------	---------------------


Data teknis	
Dimensi [mm]	Ø 58 / L = 46
Material	aluminium
Putaran maks., mekanis [U/min]	12000
Torsi awal maks. [Nm]	1
Torsi suhu referensi [°C]	20
Desain poros	poros solid
Diameter poros [mm]	6
Material poros	baja (1.4104)
Beban poros aksial maks. (di ujung poros) [N]	10
Beban poros radial maks. (di ujung poros) [N]	20
Flensa pemasangan	flensa sinkronisasi

Koneksi listrik

Kabel: 2 m, PUR; radial

coklat	A
hijau	A dibalik
abu-abu	B
merah muda	B dibalik
merah	indeks 0
hitam	indeks 0 dibalik
biru	L+ sensor
putih	0V sensor
coklat/hijau	L+ (Up)
putih/hijau	0V (Un)
ungu	kegagalan dibalik
penutup	casing

Diagram dan grafik

Diagram pulsa	 arah putaran searah jarum jam (menghadap poros)
---------------	---