

RU-0120-I05/N2

- CE

Resolusi	120 resolusi
Desain poros	poros solid
Diameter poros [mm]	6

Toleransi tegangan pengoperasian	[%]	10
Tegangan pengoperasian	[V]	5 DC
Konsumsi arus	[mA]	150

Desain kelistrikan	TTL
Beban arus maks. per output [mA]	20
Frekuensi peralihan [kHz]	300
Perbedaan fase A dan B [°]	90

Resolusi	120 resolusi
----------	--------------

Suhu sekitar	[°C]	-20...100
Suhu penyimpanan	[°C]	-30...100
Perlindungan		IP 64

Tahan guncangan	100 g (6 ms)
-----------------	--------------



Encoder inkremental dengan poros solid

RU-0120-I05/N2

Ketahanan terhadap getaran	10 g (55...2000 Hz)
----------------------------	---------------------


Data teknis	
Dimensi [mm]	Ø 58 / L = 46
Material	aluminium
Putaran maks., mekanis [U/min]	12000
Torsi awal maks. [Nm]	1
Torsi suhu referensi [°C]	20
Desain poros	poros solid
Diameter poros [mm]	6
Material poros	baja (1.4104)
Beban poros aksial maks. (di ujung poros) [N]	10
Beban poros radial maks. (di ujung poros) [N]	20
Flensa pemasangan	flensa sinkronisasi

Koneksi listrik

Kabel: 2 m, PUR; radial

coklat	A
hijau	A dibalik
abu-abu	B
merah muda	B dibalik
merah	indeks 0
hitam	indeks 0 dibalik
biru	L+ sensor
putih	0V sensor
coklat/hijau	L+ (Up)
putih/hijau	0V (Un)
ungu	kegagalan dibalik
penutup	casing

Diagram dan grafik

Diagram pulsa	 arah putaran searah jarum jam (menghadap poros)
---------------	---