


SF5300



Sensor aliran untuk koneksi ke satu unit evaluasi

SFD10ZDB /6M



1 ulir internal M18 x 1,5



Karakteristik produk

Panjang probe L	[mm]	45
Koneksi proses		M18 x 1,5 ulir internal

Aplikasi

Aplikasi		rentang suhu tinggi
Media		Cairan; Gas
Peringkat tekanan	[bar]	300

Cairan

Suhu media	[°C]	0...120
------------	------	---------

Gas

Suhu media	[°C]	0...100
------------	------	---------

Data kelistrikan

Koneksi ke monitor kontrol		VS3000
----------------------------	--	--------

Rentang pengukuran/pengaturan

Panjang probe L	[mm]	45
Cairan		
Rentang pengaturan	[cm/s]	3...300
Sensitivitas terbesar	[cm/s]	3...60
Gas		
Rentang pengaturan	[cm/s]	200...3000
Sensitivitas terbesar	[cm/s]	200...800

Akurasi/deviasi

Gradien suhu	[K/min]	300
--------------	---------	-----

Waktu respons

Waktu respons	[s]	1...10
---------------	-----	--------

Kondisi pengoperasian

Perlindungan		IP 67
--------------	--	-------


SF5300



Sensor aliran untuk koneksi ke satu unit evaluasi

SFD10ZDB /6M

Pengujian/persetujuan		
Tahan guncangan	DIN IEC 68-2-27	40 g (11 ms)
Ketahanan terhadap getaran	DIN IEC 68-2-6	10 g (55...2000 Hz)
MTTF	[ANN]	8096
Data teknis		
Berat	[g]	454.5
Casing		untuk adaptor
Dimensi	[mm]	M18 x 1.5
Penamaan ulir		M18 x 1.5
Material		Mur pengunci: baja tahan karat; Konektor kabel: FKM; mur untuk konektor kabel: kuningan berlapis nikel; Selongsong: kuningan berlapis nikel
Material yang kontak dengan media		baja tahan karat (1.4404 / 316L); O-ring: FKM 80 Shore A
Koneksi proses		M18 x 1,5 ulir internal
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 6 m, silikon; Panjang kabel maksimal: 100 m; 5 x 0.34 mm ²		
Koneksi		



	Warna core :
BN =	coklat
BU =	biru
BK =	hitam
WH =	putih
GY =	abu-abu