



Encoder inkremental dengan poros solid

RV-1000-I24/S

Produk tidak tersedia - entri arsip



- 1 tanda referensi
2 M3 kedalaman 5 mm



Karakteristik produk

Resolusi	1000 resolusi
Desain poros	poros solid
Diameter poros [mm]	10

Aplikasi

Prinsip fungsi	inkremental
----------------	-------------

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	155

Output

Desain kelistrikan	HTL
Beban arus maks. per output [mA]	50
Frekuensi peralihan [kHz]	300
Tipe pelindung hubung singkat	< 60 s
Perbedaan fase A dan B [°]	90

Rentang pengukuran/pengaturan

Resolusi	1000 resolusi
----------	---------------

Kondisi pengoperasian

Suhu sekitar [°C]	-30...70
-------------------	----------



Encoder inkremental dengan poros solid

RV-1000-I24/S

Suhu penyimpanan	[°C]	-30...100
Kelembapan udara relatif maks.	[%]	98
Perlindungan		IP 64

Pengujian/persetujuan


Tahan guncangan		100 g (11 ms)
Ketahanan terhadap getaran		10 g (58...2000 Hz)

Data teknis

Berat	[g]	360
Dimensi	[mm]	Ø 58 / L = 82.5
Material		aluminium
Putaran maks., mekanis	[U/min]	12000
Torsi awal maks.	[Nm]	1
Torsi suhu referensi	[°C]	20
Desain poros		poros solid
Diameter poros	[mm]	10
Material poros		baja (1.4104)
Beban poros aksial maks. (di ujung poros)	[N]	10
Beban poros radial maks. (di ujung poros)	[N]	20

Koneksi listrik

Konektor: 1 x M12, aksial



1	L+
2	A
3	Penutup casing
4	B
5	indeks 0
6	0V

Diagram dan grafik

Diagram pulsa



arah putaran searah jarum jam (menghadap poros)