



RV6106



Encoder inkremental dengan poros solid

RV-0500-I24/S M

Produk tidak tersedia - entri arsip



- 1 tanda referensi
2 M3 kedalaman 5 mm



Karakteristik produk

Resolusi	500 resolusi
Desain poros	poros solid
Diameter poros [mm]	10

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	150

Output

Desain kelistrikan	HTL
Beban arus maks. per output [mA]	50
Frekuensi peralihan [kHz]	300
Tipe pelindung hubung singkat	< 60 s
Perbedaan fase A dan B [°]	90

Rentang pengukuran/pengaturan

Resolusi	500 resolusi
----------	--------------

Kondisi pengoperasian

Suhu sekitar [°C]	-30...85
Suhu penyimpanan [°C]	-30...100
Kelembapan udara relatif maks. [%]	98



Encoder inkremental dengan poros solid

RV-0500-I24/S M

Perlindungan	IP 64
--------------	-------

Pengujian/persetujuan

Tahan guncangan	100 g (11 ms)
Ketahanan terhadap getaran	10 g (58...2000 Hz)

Data teknis

Dimensi	[mm]	Ø 58 / L = 82.5
Material		aluminium
Putaran maks., mekanis	[U/min]	12000
Torsi awal maks.	[Nm]	1
Torsi suhu referensi	[°C]	20
Desain poros		poros solid
Diameter poros	[mm]	10
Material poros		baja (1.4104)
Beban poros aksial maks. (di ujung poros)	[N]	10
Beban poros radial maks. (di ujung poros)	[N]	20


Koneksi listrik

Konektor: 1 x (ifm 1013.1), aksial

1	L+
2	A
3	Penutup casing
4	B
5	indeks 0
6	0V

Diagram dan grafik

Diagram pulsa



arah putaran searah jarum jam (menghadap poros)