

Encoder inkremental dengan poros solid

RV-1024-I24/L6

Produk tidak tersedia - entri arsip



- 1 tanda referensi
2 M3 kedalaman 5 mm



Karakteristik produk

Resolusi	1024 resolusi
Desain poros	poros solid
Diameter poros [mm]	10

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	95; ((max. 150); tanpa beban)

Output

Desain kelistrikan	HTL
Beban arus maks. per output [mA]	50
Frekuensi peralihan [kHz]	300
Tipe pelindung hubung singkat	< 60 s

Rentang pengukuran/pengaturan

Resolusi	1024 resolusi
----------	---------------

Kondisi pengoperasian

Suhu sekitar [°C]	-40...100
Kelembapan udara relatif maks. [%]	75; (secara singkat: 95 %; kondensasi tidak diperbolehkan)
Perlindungan	IP 64; (pada casing: IP 67; pada poros: IP 64)

Pengujian/persetujuan

Tahan guncangan	200 g (6 ms)
Ketahanan terhadap getaran	30 g (55...2000 Hz)



Encoder inkremental dengan poros solid

RV-1024-I24/L6

Data teknis		
Berat	[g]	733.8
Dimensi	[mm]	Ø 58 / L = 46.7
Material		aluminium
Putaran maks., mekanis	[U/min]	16000
Torsi awal maks.	[Nm]	1
Torsi suhu referensi	[°C]	20
Desain poros		poros solid
Diameter poros	[mm]	10
Material poros		baja (1.4104)
Beban poros aksial maks. (di ujung poros)	[N]	10
Beban poros radial maks. (di ujung poros)	[N]	20


Koneksi listrik

Kabel: 6 m, PUR; radial, juga dapat digunakan secara aksial

coklat	A
hijau	A dibalik
abu-abu	B
merah muda	B dibalik
merah	indeks 0
hitam	indeks 0 dibalik
biru	L+ sensor
putih	0V sensor
coklat/hijau	L+ (Up)
putih/hijau	0V (Un)
ungu	kegagalan dibalik
penutup	casing

Diagram dan grafik

Diagram pulsa



Output A

Output B

indeks 0