


Sensor aliran untuk koneksi ke satu unit evaluasi

SFG18ABBE1

Produk tidak tersedia - entri arsip



Karakteristik produk

Koneksi proses	ANSIB 16.5 (1 in; 300 lb/sq.in)
----------------	---------------------------------

Aplikasi

Aplikasi	Eks zona 1
----------	------------

Suhu media	[°C]	-25...80
------------	------	----------

Peringkat tekanan	[bar]	30
-------------------	-------	----

Cairan

Aplikasi	Eks zona 1
----------	------------

Suhu media	[°C]	-25...80
------------	------	----------

Gas

Suhu media	[°C]	-25...80
------------	------	----------

Data kelistrikan

Koneksi ke monitor kontrol	VS 0200 Exi
----------------------------	-------------

Rentang pengukuran/pengaturan

Cairan

Rentang pengaturan	[cm/s]	3...300
--------------------	--------	---------

Sensitivitas terbesar	[cm/s]	3...60
-----------------------	--------	--------

Gas

Rentang pengaturan	[cm/s]	200...2000
--------------------	--------	------------

Sensitivitas terbesar	[cm/s]	200...800
-----------------------	--------	-----------

Akurasi/deviasi

Gradien suhu	[K/min]	15
--------------	---------	----

Waktu respons


Waktu respons	[s]	1...10
---------------	-----	--------



Sensor aliran untuk koneksi ke satu unit evaluasi

SFG18ABBE1

Cairan		
Waktu respons	[s]	1...10
Gas		
Waktu respons	[s]	1...10
Kondisi pengoperasian		
Perlindungan		IP 67
Data teknis		
Casing		berbentuk silinder
Dimensi	[mm]	Ø 18
Material		baja tahan karat (1.4571 / 316Ti)
Material yang kontak dengan media		baja tahan karat (1.4571 / 316Ti)
Koneksi proses		ANSIB 16.5 (1 in; 300 lb/sq.in)
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 2 m, TPE-S; Panjang kabel maksimal: 100 m; 5 x 0.34 mm ²		
Koneksi		



Warna core :

BN = coklat

BU = biru

BK = hitam

WH = putih

GY = abu-abu