


ZZ1060



Interface IO-Link

SET AL1060 IO-Link Master USB



- 1 IO-Link
- 2 AUX
- 3 USB

Aplikasi		
Aplikasi	pengaturan parameter dan analisis unit	
Data kelistrikan		
Tegangan nominal DC	[V]	5; (USB)
Konsumsi arus	[mA]	< 1100; (USB)
Kelas perlindungan		III
Suplai sensor		24 V DC
Suplai sensor - AUX		
Peringkat arus per port	[A]	0.65
Suplai sensor - USB		
Peringkat arus per port	[A]	0.15
Input/output		
Jumlah input dan output	Jumlah input digital: 2; Jumlah output digital: 2	
Input		
Jumlah input digital	2; (Port IO-Link Class A : 1 x 2)	
Level peralihan tinggi	[V]	11...30
Level peralihan rendah	[V]	0...5
Input digital pelindung hubung singkat		ya
Output		
Jumlah output digital	2; (Port IO-Link Class A: 1 x 2)	
Beban arus maks. per output	[mA]	150



Interface IO-Link

SET AL1060 IO-Link Master USB

Tahan dari hubung singkat	ya	
Interface		
Interface komunikasi	IO-Link; USB	
Jumlah interface USB	1	
IO-Link Master		
Tipe transmisi	COM1 (4,8 kBaud); COM2 (38,4 kBaud); COM3 (230,4 kBaud)	
Revisi O-Link	1.1	
Jumlah port kelas A	1	
USB		
Versi	USB 2.0	
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...50
Suhu penyimpanan	[°C]	-25...85
Kelembapan udara relatif maks.	[%]	90
Perlindungan	IP 65; IP 67	
Pengujian/persetujuan		
EME	DIN EN 61000-6-2	
	DIN EN 61000-6-4	
Tahan guncangan	DIN EN 60068-2-27	
Ketahanan terhadap getaran	DIN EN 60068-2-64	
	DIN EN 60068-2-6	
Data teknis		
Berat	[g]	388.3
Material	casing: PA; soket: PA; mur pengunci: kuningan berlapis nikel	
Material penyegel	FKM	
Elemen display/pengoperasian		
Display	PWR	1 x LED, hijau/merah suplai tegangan
	IO-Link	1 x LED, hijau/merah komunikasi
	DI/DO	1 x LED, oranye input/output digital
Aksesori		
Item dikirim	Master IO-Link dengan interface USB: 1, AL1060	
	Kabel koneksi: 1 m, M12 dengan kode A, EVC012	
	Kabel USB: 1 m, M12 dengan kode B, E12689	
Aksesori (opsional)	Suplai daya mode switch 24 V DC:, M12 dengan kode A, E80121	
Keterangan		
Jumlah paket	1 buah	



Interface IO-Link

SET AL1060 IO-Link Master USB

Koneksi listrik - AUX


Konektor: M12; pengkodean: A



- | | |
|----|-----------------|
| 1: | + 24 V DC US |
| 2: | tidak digunakan |
| 3: | GND US |
| 4: | tidak digunakan |

Koneksi listrik - IO-Link

Konektor: M12; pengkodean: A; Segel: FKM



- | | |
|----|----------------------|
| 1: | Suplai sensor US L+ |
| 2: | input/output digital |
| 3: | Suplai sensor US L- |
| 4: | IO-Link (C/Q) |
| 5: | tidak digunakan |

Koneksi listrik - USB

; pengkodean: B



- | | |
|----|---------------|
| 1: | VBUS + 5 V DC |
| 2: | Data - |
| 3: | Data + |
| 4: | GND |