


Pemantau aliran

SID10ADT100G/US-100-IAZ

Produk tidak tersedia - entri arsip



- 1 ulir internal M18 x 1.5
2 tombol tekan pengaturan



Karakteristik produk

Jumlah input dan output	Jumlah output analog: 1
Koneksi proses	M18 x 1,5 ulir internal

Aplikasi

Media	Cairan; media agresif
Suhu media [°C]	-25...80
Peringkat tekanan [bar]	300

Cairan

Suhu media [°C]	-25...80
-----------------	----------

Data kelistrikan

Tegangan pengoperasian [V]	20...36 DC; (sesuai SELV/PELV)
Konsumsi arus [mA]	< 90; (tanpa beban)
Pelindung polaritas terbalik	ya
Waktu penundaan pengaktifan [s]	15; (diindikasikan secara optis)

Input/output

Jumlah input dan output	Jumlah output analog: 1
-------------------------	-------------------------

Output

Jumlah total output	1
Sinyal output	sinyal analog
Jumlah output analog	1



Pemantau aliran

SID10ADT100G/US-100-IAZ

Output arus analog	[mA]	4...20
Beban maks.	[Ω]	500
Pelindung beban berlebih		ya

Rentang pengukuran/pengaturan

Cairan		
Rentang pengaturan	[cm/s]	3...60

Waktu respons

Waktu respons	[s]	1...10
---------------	-----	--------

Cairan		
Waktu respons	[s]	1...10

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67

Pengujian/persetujuan

Tahan guncangan	DIN IEC 68-2-27	50 g (11 ms)
Ketahanan terhadap getaran	DIN EN 60068-2-6	20 g (55...2000 Hz)

Data teknis

Dimensi	[mm]	M18 x 1.5
Penamaan ulir		M18 x 1.5
Material		PBT-GF20
Material yang kontak dengan media		titanium (3.7035); O-ring: FPM 8 x 1,5 gr 80° Shore A
Koneksi proses		M18 x 1,5 ulir internal

Elemen display/pengoperasian

Display	fungsi	10 x LED, 2 warna
---------	--------	-------------------

Keterangan

Jumlah paket		1 buah
--------------	--	--------

Koneksi listrik

Konektor: 1 x M12; pengkodean: A





Pemantau aliran

SID10ADT100G/US-100-IAZ

Koneksi

