

Sensor aliran untuk koneksi ke satu unit evaluasi

STM12ABA

Produk tidak tersedia - entri arsip



Karakteristik produk

Koneksi proses	M12 x 1
----------------	---------

Aplikasi

Aplikasi	rentang suhu tinggi
Media	Cairan; Gas
Suhu media [°C]	-25...80
Peringkat tekanan [bar]	30

Cairan

Aplikasi	rentang suhu tinggi
Suhu media [°C]	-25...80

Gas

Suhu media [°C]	-25...80
-----------------	----------

Data kelistrikan

Koneksi ke monitor kontrol	VS 0100
----------------------------	---------

Rentang pengukuran/pengaturan

Cairan

Rentang pengaturan [cm/s]	3...300
Sensitivitas terbesar [cm/s]	3...60

Gas

Rentang pengaturan [cm/s]	5...1500
---------------------------	----------

Akurasi/deviasi

Gradien suhu [K/min]	15
----------------------	----

Waktu respons

Waktu respons [s]	1...10
-------------------	--------

Cairan

Waktu respons [s]	1...10
-------------------	--------

Gas

Waktu respons [s]	1...10
-------------------	--------

Kondisi pengoperasian

Perlindungan	IP 67
--------------	-------

ST1000



Sensor aliran untuk koneksi ke satu unit evaluasi

STM12ABA


Data teknis	
Casing	tipe berulir
Dimensi [mm]	M12 x 1
Penamaan ulir	M12 x 1
Material	baja tahan karat (1.4305/303)
Koneksi proses	M12 x 1

Keterangan	
Jumlah paket	1 buah

Koneksi listrik

Kabel: 2 m, Silflex-PUR; Panjang kabel maksimal: 100 m; 4 x 0.25 mm²

Koneksi



Warna core :
BN = coklat
GN = hijau
WH = putih
YE = kuning