


TS2256



Sensor kabel suhu dengan koneksi proses

TS-200KCID06-...../US/ IV



Karakteristik produk

Rentang pengukuran	-50...250 °C	-58...482 °F
Koneksi proses	Ø 6 mm	
Panjang pemasangan EL [mm]	50	

Aplikasi

Elemen pengukuran	1 x Pt 100; (sesuai DIN EN 60751, kelas A)	
Media	cairan dan gas	
Kedalaman pemasangan minimal [mm]	15	

Data kelistrikan

Kelas perlindungan	III
--------------------	-----

Rentang pengukuran/pengaturan

Panjang probe L [mm]	50	
Rentang pengukuran	-50...250 °C	-58...482 °F
Catatan tentang rentang pengukuran	stasioner: 280 °C / 536 °F (10000 h)	

Akurasi/deviasi

Akurasi [K]	$\pm (0,15 K + 0,002 \times t)$
-------------	-----------------------------------

Waktu respons

Respons dinamis T05 / T09 [s]	11 / 37; (sesuai DIN EN 60751)
-------------------------------	--------------------------------

Kondisi pengoperasian

Perlindungan	IP 67
--------------	-------

Pengujian/persetujuan

MTTF [ANN]	11415.5
------------	---------

Data teknis

Berat [g]	72.7
Dimensi [mm]	Ø 6
Material	baja tahan karat (1.4571 / 316Ti); PFA/PTFE
Material yang kontak dengan media	baja tahan karat (1.4571 / 316Ti)
Koneksi proses	Ø 6 mm
Diameter probe [mm]	6
Panjang pemasangan EL [mm]	50

TS2256



Sensor kabel suhu dengan koneksi proses

TS-200KCID06-...../US/ IV

Keterangan

Keterangan	Nilai akurasi berlaku untuk air yang mengalir.
Jumlah paket	1 buah

Koneksi listrik

Kabel: 2 m, PTFE

Konektor: 1 x M12; pengkodean: A



Koneksi

