


Sensor induktif

IFA2004-ARKG/20M/PVC/INOX

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	4
Casing	tipe berulir
Dimensi [mm]	M12 x 1

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output



Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	5.6
Arus beban minimal [mA]	4
Kebocoran arus maks. [mA]	0.6
Peringkat arus permanen dari output peralihan DC [mA]	400
Frekuensi peralihan DC [Hz]	1500
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa



Sensor induktif

IFA2004-ARKG/20M/PVC/INOX

Pelindung beban berlebih		ya	
Zona pendeteksian			
Jangkauan pendeteksian	[mm]	4	
Jangkauan pendeteksian real Sr	[mm]	4 ± 10 %	
Jarak pengoperasian	[mm]	0...3.25	
Akurasi/deviasi			
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis	[X01]	1...15	
Deviasi titik peralihan	[X01]	-10...10	
Kondisi pengoperasian			
Suhu sekitar	[°C]	-25...80	
Perlindungan		IP 67	
Pengujian/persetujuan			
EME	EN 60947-5-2		kelas B
	EN 55011		
Data teknis			
Casing		tipe berulir	
Pemasangan		non-flush mountable	
Dimensi	[mm]	M12 x 1	
Penamaan ulir		M12 x 1	
Material		PBT; baja tahan karat (1.4404 / 316L)	
Elemen display/pengoperasian			
Display	status peralihan	1 x LED, kuning	
Keterangan			
Jumlah paket		1 buah	
Koneksi listrik			
Kabel: 20 m, PVC			
Koneksi			



Warna core :
 BN = coklat
 BU = biru