

DX2001




Multifunction display for monitoring revolution, speed and time

DISPLAY/FX360

Article no longer available - archive entry

Alternative articles: DX2021
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application	universal evaluation and display for all physical units which can be derived from pulse sequences	
Electrical data		
Frequency AC	[Hz]	50...60
Operating voltage tolerance	[%]	33...58
Operating voltage	[V]	230 / 115 AC / 24 DC
Current consumption	[mA]	120 (18 V); 95 (24 V); 80 (30 V)
Auxiliary energy for sensors DC	[V]	24; (±15 %, 150 mA)
Operating conditions		
Ambient temperature	[°C]	0...45
Storage temperature	[°C]	-25...75
Protection		IP 65; (on the front)
Protection rating terminals		IP 20
Tests / approvals		
EMC	EN 50081-1	
	EN 61000-6-2	
Mechanical data		
Weight	[g]	565.2

DX2001



Multifunction display for monitoring revolution, speed and time

DISPLAY/FX360

Materials

Noryl UL94-V-0

Displays / operating elements

Display

7-segment LED display, orange 6-digit 15 mm

Electrical connection

screw terminals, DC: 10 x ...1.5 mm²

screw terminals, AC: 4 x ...2.5 mm²

Connection

