




QA0011

LR DEVICE (USB Stick)



Produktmerkmale

LR DEVICE (USB-Stick)

Parametrieren der Geräte über das Netzwerk

Software zur übersichtlichen On- und Offline-Parametrierung von IO-Link-Sensoren mittels USB Adapter

Anwendung über USB Anschlusskabel (Treiber werden mitgeliefert): IO-Link Interface E30396 oder IO-Link Master E30390 (jeweiliges Datenblatt beachten)

IODD Import und Update von der ifm Homepage

Einlesen von IODD's über Speichermedien

Automatische Identifizierung der Sensoren

Grafische Darstellung der Prozesswerte und Historienverlauf inkl. Exportfunktion

Dokumentation und Archivierung

Übertragbare Parametersätze

Vollständiger Memory Plug Support für IO-Link 1.1

Mechanische Daten

Gewicht	[kg]	0,14
---------	------	------

Bemerkungen

Verpackungseinheit	[Stück]	1
--------------------	---------	---

Weitere Daten


Systemvoraussetzungen

Windows 7 SP1, Windows 8.1, Windows 10, Windows Server 2008 R2 SP1, Windows Server 2012, Windows Server 2012 R2, Windows Server 2016
CPU Intel Dual Core 2.0 GHz
2 GB RAM
5 GB freier Festplattenspeicherplatz
Webbrowser (Chrome, Firefox, Internet Explorer 11, Microsoft Edge)



QA0011

LR DEVICE (USB Stick)



Product characteristics

LR DEVICE (USB stick)

Parameter setting of the units via the network

Software for clear online and offline parameter setting of IO-Link sensors via USB adapter

Use via USB connection cable (drivers are supplied): E30396 IO-Link interface or E30390 IO-Link master (note the respective data sheet)

IODD import and update from ifm's homepage

Reading of IODDs via storage media

Automatic sensor identification

Graphic representation of the process values and history incl. export function

Documentation and archiving

Transferable parameter sets

Full memory plug support for IO-Link 1.1

Mechanical data

Weight	[kg]	0.14
--------	------	------

Remarks

Pack quantity	[piece]	1
---------------	---------	---

Other data

System requirements	Windows 7 SP1, Windows 8.1, Windows 10, Windows Server 2008 R2 SP1, Windows Server 2012, Windows Server 2012 R2, Windows Server 2016 CPU Intel dual core 2.0 GHz 2 GB RAM 5 GB free hard disk space Web browser (Chrome, Firefox, Internet Explorer 11, Microsoft Edge)
---------------------	---