


Fibre optic through-beam sensor

FE-00-A-A-M4/1M

Article no longer available - archive entry



Application

Function principle	Through-beam sensor
--------------------	---------------------

Detection zone

Range with fibre-optic amplifier type	OKF; OUF
---------------------------------------	----------

OKF

Range of fibre optics [mm]	120
----------------------------	-----

OUF

Range of fibre optics [mm]	120
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-40...290
--------------------------	-----------

Mechanical data

Weight [g]	74
Version of sensing head	straight
Sensing head thread	M4
Sensing head length [mm]	15
Total length [mm]	1000
Min. bending radius [mm]	20; (for fixed installation)
Fibre arrangement	

**Fibre optic through-beam sensor**

FE-00-A-A-M4/1M

Materials	Adapter: ABS
Fibre material	glass
Fibre head material	aluminium
Fibre sheath material	aluminium
Accessories	
Items supplied	hexagon nuts: 4 x M4
	tooth lock washers: 4
	knurled nut: 1 x M11
Remarks	
Pack quantity	1 pcs.