




Inductive sensor

IFK2007-BRKG/M/60V/8M/HH



Product characteristics

Electrical design	PNP/NPN
Output function	normally closed
Sensing range [mm]	7
Housing	threaded type
Dimensions [mm]	M12 x 1 / L = 79

Application

Special feature	Increased sensing range
Application	Use in mobile and harsh applications

Electrical data

Operating voltage [V]	10...60 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Minimum load current [mA]	2
Max. leakage current [mA]	0.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	300
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	7
Real sensing range S_r [mm]	$7 \pm 10 \%$
Operating distance [mm]	0...5.67
Increased sensing range	yes



Inductive sensor

IFK2007-BRKG/M/60V/8M/HH

Accuracy / deviations				
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.5 / copper: 0.4		
Hysteresis	[% of Sr]	1...20		
Switch point drift	[% of Sr]	-10...10		
Operating conditions				
Ambient temperature		[°C]	-40...85	
Protection		IP 67; IP 69K		
Tests / approvals				
EMC		automotive area		
		noise emission and noise interference: ECE R10		E1 type approval
		noise immunity according to DIN ISO 11452-2		100 V/m
		conducted interference in 24 V networks to ISO 7637-2: 2004 (pulse 1 to 4) and ISO16750-2: 2012 (load dump)		
		pulse		1 2a 2b 3a 3b 4 Load dump
		severity level		III III III III III Test A
		failure criterion		C A C A A C C
		EN 61000-4-2 ESD		4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated		10 V/m
		EN 61000-4-4 Burst		2 kV
		EN 61000-4-5 Surge		0,5 kV mains line to line
		EN 61000-4-6 HF conducted		10 V
		EN 55011		class B
Vibration resistance		EN 60068-2-6 Fc	20 g (10...3000 Hz) / -20...50 °C	
			50 sweep cycles, 1 octave per minute, in 3 axes	
Shock resistance		EN 60068-2-27 Ea	100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes / -40...85 °C	
Continuous shock resistance		EN 60068-2-27	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes / -20...50 °C	
Fast temperature change		EN 60068-2-14 Na	TA = -40 °C; TB = 85 °C; t1 = 30 min; t2 = < 10 s; 50 cycles	
Salt spray test		EN 60068-2-52 Kb	severity level 5 (4 test cycles)	
MTTF		[years]	695	
Mechanical data				
Weight		[g]	349	
Housing		threaded type		
Mounting		non-flush mountable		
Dimensions		[mm]	M12 x 1 / L = 79	
Thread designation		M12 x 1		
Materials		housing: stainless steel; sensing face: LCP natural; LED window: PEI; lock nuts: brass		
Displays / operating elements				
Display		switching status	4 x 90° LED, yellow	
Accessories				
Items supplied		lock nuts: 2		

IFM212



Inductive sensor

IFK2007-BRKG/M/60V/8M/HH

Remarks


Pack quantity

1 pcs.

Electrical connection

Cable: 8 m, PUR; 2 x 0.5 mm²

Connection



BK = Core colours :
black
WH = white