




Inductive sensor

IIC4015-CPKG/30M

Article no longer available - archive entry



Product characteristics

Electrical design	PNP
Output function	complementary
Sensing range [mm]	15
Housing	threaded type
Dimensions [mm]	M30 x 1.5

Application

Special feature	Halogen-free
-----------------	--------------

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	complementary
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	250
Short-circuit protection	yes

**Inductive sensor**

IIC4015-CPKG/30M

Type of short-circuit protection	pulsed	
Overload protection	yes	
Detection zone		
Sensing range	[mm]	15
Real sensing range Sr	[mm]	15 ± 10 %
Operating distance	[mm]	0...12.1
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	3...15
Switch point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 68	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	threaded type	
Mounting	non-flush mountable	
Dimensions	[mm]	M30 x 1.5
Thread designation	M30 x 1.5	
Materials	PBT; TPE-E	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	




Inductive sensor

IIC4015-CPKG/30M

Electrical connection

Cable: 30 m, PUR, Halogen-free; 4 x 0.34 mm²

Connection



BK =	Core colours :
BN =	black
BU =	brown
WH =	blue
	white