




Inductive high-temperature sensor

IIA4015ZCPKG/6M/SH



Product characteristics		
Electrical design		PNP
Output function		complementary
Sensing range	[mm]	15
Housing		threaded type
Dimensions	[mm]	M30 x 1.5
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		complementary
Max. voltage drop switching output DC	[V]	2.5
Max. leakage current	[mA]	0.5
Permanent current rating of switching output DC	[mA]	70
Switching frequency DC	[Hz]	250
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes



Inductive high-temperature sensor

IIA4015ZCPKG/6M/SH

Detection zone		
Sensing range	[mm]	15
Real sensing range Sr	[mm]	15 ± 10 %
Operating distance	[mm]	0...12.1
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...20
Switch point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	0...130
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5 kV line to line, Ri: 2 Ohm
	EN 61000-4-6 HF conducted	10 V
	EN 55011 emission	class B
MTTF	[years]	1361
Mechanical data		
Weight	[g]	399.5
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M30 x 1.5
Thread designation		M30 x 1.5
Materials		threaded sleeve: stainless steel; sensing face: PBT; end cap: TPE
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.




Inductive high-temperature sensor

IIA4015ZCPKG/6M/SH

Electrical connection

Cable: 6 m, silicone, Ø 5.4 mm; 4 x 0.34 mm²

Connection



BK =	Core colours :
BN =	black
BU =	brown
WH =	blue
	white