


KT5311



Illuminated capacitive touch sensor

KTMDF-EGRBPKG/US/0,3m



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	Ø 32 / L = 31

Application

Operating principle	dynamic
---------------------	---------

Electrical data

Operating voltage [V]	12...30 DC
Current consumption [mA]	30
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	500

Outputs

Electrical design	PNP
Output function	normally open
Permanent current rating of switching output DC [mA]	200
Short-circuit protection	yes
Overload protection	yes
Length of output signal [ms]	300

Response times

Response time [ms]	35
--------------------	----

Operating conditions

Ambient temperature [°C]	-40...85
Protection	IP 65; IP 67; IP 69K; (on the front)

Tests / approvals


EMC	IEC 61000-4
-----	-------------

KT5311



Illuminated capacitive touch sensor

KTMDF-EGRBPKG/US/0,3m

Mechanical data		
Weight	[g]	76.5
Dimensions	[mm]	Ø 32 / L = 31
Materials	stainless steel (316L/1.4404); active face: PA Grilamid TR 90UV	
Displays / operating elements		
Display	switching status	1 x LED, red
	function	1 x LED, green can be triggered
Accessories		
Items supplied	lock nuts: 1	
	Gasket: 1	
Accessories (optional)	symbol disc	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 0.3 m, PUR		
Connection		
		
Connector: 1 x M12		