




External illumination

RINGLIGHT 106x66 W/0,3M/US



Product characteristics

Type of light	white light
---------------	-------------

Application

Illuminated field [mm]	Ø 106 / Ø 66; (external / internal)
Design	ring
Type of operation	high light intensity (pulsed, permanent operation with cooling only); normal light intensity (permanent operation possible)

Electrical data

Operating voltage [V]	24 DC
Current consumption [mA]	operating mode "permanent operation": 800; operating mode "high light intensity": 1200
Type of light	white light
Colour temperature [K]	5600

Inputs

Trigger	24 V PNP
---------	----------

Detection zone

Angle of aperture cylindrical [°]	120
-----------------------------------	-----

Operating conditions

Ambient temperature [°C]	-10...55
Storage temperature [°C]	-25...75



External illumination

RINGLIGHT 106x66 W/0,3M/US

Protection	IP 65
Overheat protection	yes; (deactivation at 65...75 °C)

Tests / approvals

Photobiological safety	exempt group; (DIN EN 62471:2008)
------------------------	-----------------------------------

Mechanical data

Weight	[g]	488
Dimensions	[mm]	Ø 122 / L = 20.5
Materials		aluminium black anodised
Lens material		glass

Displays / operating elements

Display		combined LED, three-colour
	illumination status	yellow
	operation	green
	excess temperature	red

Remarks

Pack quantity	1 pcs.
---------------	--------


Electrical connection

Cable: 0.3 m, PUR, black; 4 x 0.34 mm²

Connector: 1 x M12; coding: A



Connection



- 4 trigger
2 operating mode "high light intensity"