



Retro-reflective sensor

OGP-FNKG/US-100 MIT 90GRAD WKL

Article no longer available - archive entry

No scale drawing available

Product characteristics

Type of light	red light
Housing	threaded type

Application

Special feature	Gold-plated contacts
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 32
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		NPN
Output function		light-on/dark-on mode; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Max. voltage drop of function check output	[V]	3.5
Max. current load for function check output	[mA]	10
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	500
Short-circuit protection		yes

OG5078



Retro-reflective sensor

OGP-FNKG/US-100 MIT 90GRAD WKL

Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone	
Range [m]	< 2.5; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes

Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 67

Tests / approvals	
EMC	EN 60947-5-2

Mechanical data	
Housing	threaded type
Dimensions [mm]	M18 x 1
Thread designation	M18 x 1
Materials	PBT
Lens material	PMMA

Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red

Accessories	
Items supplied	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated






Retro-reflective sensor

OGP-FNKG/US-100 MIT 90GRAD WKL

Connection



2

Function check output