

# SF0540




## Flow sensor for connection to an evaluation unit

SFR14XBK/16M

phase-out article

Alternative articles: SF2410

When selecting an alternative article and accessories please note that technical data may differ!



1 tightening torque max. 8 Nm



### Product characteristics

Probe length L	[mm]	12
Process connection		G 1/4 external thread

### Application

Media		Liquids; aggressive media
Medium temperature	[°C]	5...70
Pressure rating	[bar]	30

### Liquids

Medium temperature	[°C]	5...70
--------------------	------	--------

### Electrical data

Connection to control monitor		VS3000
-------------------------------	--	--------

### Measuring/setting range

Probe length L	[mm]	12
Liquids		
Setting range	[cm/s]	3...60
Greatest sensitivity	[cm/s]	3...40

### Accuracy / deviations

Temperature gradient	[K/min]	7
----------------------	---------	---

### Response times

Response time	[s]	2...20
---------------	-----	--------

### Liquids

Response time	[s]	2...20
---------------	-----	--------

### Operating conditions

Protection		IP 67
------------	--	-------

### Tests / approvals

Shock resistance	DIN IEC 68-2-27	40 g (11 ms)
------------------	-----------------	--------------

# SF0540



## Flow sensor for connection to an evaluation unit

SFR14XBK/16M

Vibration resistance	DIN IEC 68-2-6	10 g (55...2000 Hz)
MTTF [years]		8648

### Mechanical data

Weight [g]	1112.8
Housing	threaded type
Materials	ceramics (99.7 % Al <sub>2</sub> O <sub>3</sub> )
Materials (wetted parts)	ceramics (99.7 % Al <sub>2</sub> O <sub>3</sub> )
Process connection	G 1/4 external thread
Installation length EL [mm]	27

### Accessories

Items supplied	sealings: 1, PTFE
----------------	-------------------


### Remarks

Remarks	For sealing use the supplied PTFE packing washer.
Pack quantity	1 pcs.

### Electrical connection

Cable: 16 m, PUR; Maximum cable length: 100 m; 5 x 0.34 mm<sup>2</sup>, PVC

### Connection



	Core colours :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey