


RM3008



Absolute multiturn encoder with hollow shaft

RM-0025-E24/E-U



Product characteristics

Resolution	8192 steps; 4096 revolutions; 25 bit
Communication interface	PROFIBUS DP
Shaft design	hollow shaft open to one side
Shaft diameter [mm]	12

Application

Function principle	absolute
Revolution type	multiturn

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	100; ((24 V))
Reverse polarity protection		yes

Outputs

Code	binary
------	--------

Measuring/setting range

Resolution	8192 steps; 4096 revolutions; 25 bit
------------	--------------------------------------

Software / programming

Parameter setting options	counting direction of the code values; Resolution; zero point; limit switches HI and LO; motion indicator; separation multiturn/singleturn
Diagnostic functions	alarms; warnings; status; serial number of the encoder
Addressing	address selector switch; 0...126



Absolute multiturn encoder with hollow shaft

RM-0025-E24/E-U

Interfaces		
Communication interface		PROFIBUS DP
PROFIBUS DP		
Transmission standard		DPV2
Operating conditions		
Ambient temperature	[°C]	-40...85
Max. relative air humidity	[%]	98
Protection		IP 67; (on the housing: IP 67; on the shaft: IP 67)
Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		10 g (10...2000 Hz)
MTTF	[years]	13.5
Mechanical data		
Weight	[g]	648
Dimensions	[mm]	Ø 58.5 / L = 99
Materials		aluminium; clamping ring: brass
Max. revolution, mechanical	[U/min]	12000
Shaft design		hollow shaft open to one side
Shaft diameter	[mm]	12
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	40
Max. shaft load radial (at the shaft end)	[N]	110
Fixing flange		Stator coupling
Electrical connection		
terminal strip in the terminal chamber:		