


# E10617



## Connection cable

VDOAF032ZDS00,6A03STGH030ZDS

Article no longer available - archive entry



### Electrical data

|                   |     |            |
|-------------------|-----|------------|
| Operating voltage | [V] | 10...30 DC |
| Protection class  |     | III        |

### Outputs

|                   |     |
|-------------------|-----|
| Electrical design | PNP |
|-------------------|-----|

### Operating conditions

|                     |      |          |
|---------------------|------|----------|
| Ambient temperature | [°C] | -25...90 |
| Protection          |      | IP 68    |

### Mechanical data

|                       |      |                             |
|-----------------------|------|-----------------------------|
| Dimensions            | [mm] | 15 x 15 x 46                |
| Materials             |      | PUR                         |
| Moulded-body material |      | PUR                         |
| Material nut          |      | diecast zinc, nickel-plated |

### Displays / operating elements

|         |                  |                 |
|---------|------------------|-----------------|
| Display | switching status | 1 x LED, yellow |
|         | operation        | 1 x LED, green  |

### Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

## Connection cable

VDOAF032ZDS00,6A03STGH030ZDS

### Electrical connection - plug


Connector: 1 x M12, straight; coding: A; Moulded body: PUR; Locking: diecast zinc, nickel-plated



### Electrical connection

Cable: 0.6 m, PUR / PVC; 3 x 0.34 mm<sup>2</sup> (182 x Ø 0.05 mm )


#### Connection



### Electrical connection - Buchse



#### Connection



# E10617



## Connection cable

VDOAF032ZDS00,6A03STGH030ZDS

### Electrical connection - socket

Connector: 1 x M8, angled; Moulded body: PUR; Locking: diecast zinc, nickel-plated