




Inductive sensor

IGB2008BAROG/UP/2LED/3M/PH

Article no longer available - archive entry

Alternative articles: IGS312
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP/NPN
Output function		normally open
Sensing range	[mm]	8
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 43
Application		
Special feature		Increased sensing range; Optical setting aid
Electrical data		
Operating voltage	[V]	10...36 DC
Protection class		II
Reverse polarity protection		no
Outputs		
Electrical design		PNP/NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	5
Minimum load current	[mA]	5
Max. leakage current	[mA]	1
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	100
Short-circuit protection		no
Overload protection		no
Detection zone		
Sensing range	[mm]	8
Real sensing range Sr	[mm]	8 ± 10 %
Increased sensing range		yes



Inductive sensor

IGB2008BAROG/UP/2LED/3M/PH

Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / aluminium: 0.4 / copper: 0.3	
Hysteresis [% of Sr]	3...15	
Operating conditions		
Ambient temperature [°C]	-25...70	
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Weight [g]	168.7	
Housing	threaded type	
Mounting	flush mountable	
Dimensions [mm]	M18 x 1 / L = 43	
Thread designation	M18 x 1	
Materials	brass white bronze coated; PBT	
Displays / operating elements		
Display	switching status	1 x LED, red
	switching status	1 x LED, green
Optical setting aid	yes	
Accessories		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 3 m, PUR / PVC; 2 x 0.50 mm²		
Connection		



BK = Core colours :
black