




Retro-reflective sensor

OLP-FKOA/SL/LS-500



1 pushbutton



Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Special feature		polarisation filter
Function principle		Retro-reflective sensor
Electrical data		
Frequency AC	[Hz]	47...63
Operating voltage	[V]	20...250 AC/DC
Max. power consumption	[VA]	4
Protection class		I
Reverse polarity protection		no
Type of light		red light
Wave length	[nm]	660
Typ. lifetime	[h]	100000
Reference temperature for service life	[°C]	25
Outputs		
Electrical design		relay
Output function		light-on/dark-on mode; (programmable)
Contact rating		250 V AC / 3 A / 960 VA, 125 V DC / 5 A / 120 W
Switching frequency AC	[Hz]	10
Switching frequency DC	[Hz]	10



Retro-reflective sensor

OLP-FKOA/SL/LS-500

Short-circuit proof	no
Overload protection	no

Detection zone

Range referred to prismatic reflector [m]	0.3...5; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes
Polarisation filter available	yes

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF [years]	256	

Mechanical data

Weight [g]	202.5
Housing	rectangular
Dimensions [mm]	75 x 27 x 62
Materials	PA; PBT
Lens material	PMMA
Lens alignment	side lens

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red

Electrical connection


Required protection	miniature fuse to IEC60127-2 sheet 1; ≤ 5 A; fast acting
---------------------	--

Remarks

Remarks	Recommendation: Check the safe functioning of the unit after a short circuit.
Pack quantity	1 pcs.

Electrical connection


Connector: 1 x 7/8"; coding: A



Retro-reflective sensor

OLP-FKOA/SL/LS-500


Connection



Note : miniature fuse to IEC60127-2 sheet 1 ≤ 5 A fast acting

Diagrams and graphs

excess gain graph



x: distance [mm]

y: Funktionsreservefaktor