




Through-beam sensor receiver

OSE-FPKG



Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage [V]	10...55 DC
Current consumption [mA]	20; ((24 V))
Protection class	II
Reverse polarity protection	yes
Type of light	infrared light
Wave length [nm]	880

Outputs

Electrical design	PNP
Output function	light-on/dark-on mode; (programmable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	100
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes



Through-beam sensor receiver

OSE-FPKG

Detection zone		
Transmitter / receiver	receiver	
Range [m]	< 20	
Range adjustable	yes	
Operating conditions		
Ambient temperature [°C]	-25...80	
Protection	IP 65	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF [years]	618	
Mechanical data		
Weight [g]	274.5	
Housing	rectangular	
Dimensions [mm]	80 x 28 x 95	
Materials	PPO modified	
Lens material	glass	
Lens alignment	side lens	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied	Angle bracket: 1, E20210 screwdrivers	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
terminals: ...1.5 mm²; Cable gland: M20 X 1.5		
Connection		

