




Pressure transmitter

PT-025-SEG14-A-ZVG/VE



1 Sealing



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1		
Measuring range	0...25 bar	0...360 psi	0...2.5 MPa
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)		

Application

Measuring element	metallic thin film cell		
Application	for mobile applications; for industrial applications		
Media	liquids and gases		
Medium temperature [°C]	-40...125		
Min. bursting pressure	600 bar	8700 psi	60 MPa
Pressure rating	65 bar	940 psi	6.5 MPa
Note on pressure rating	static		
Vacuum resistance [mbar]	-1000		
Type of pressure	relative pressure		

Electrical data

Operating voltage [V]	8...36 DC		
Min. insulation resistance [MΩ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		
Power-on delay time [s]	< 0.1		

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Outputs

Total number of outputs	1
Output signal	analogue signal
Number of analogue outputs	1



Pressure transmitter

PT-025-SEG14-A-ZVG/VE

Analogue current output		[mA]		4...20	
Max. load		[Ω]		(Ub - 8 V) / 21,5 mA ; @8V= 0 Ω ; @12V max. 200 Ω: @24V max. 750 Ω	
Short-circuit proof				yes	
Overload protection				yes	
Measuring/setting range					
Measuring range		0...25 bar		0...360 psi	
				0...2.5 MPa	
Accuracy / deviations					
Repeatability		[% of the span]		< ± 0,05; (with temperature fluctuations < 10 K)	
Characteristics deviation		[% of the span]		< ± 0,5; (incl. drift when overtightened, zero point and span error, non-linearity, hysteresis)	
Linearity deviation		[% of the span]		< ± 0,1 (BFSL) / < ± 0,2 (LS)	
Hysteresis deviation		[% of the span]		< ± 0,2	
Long-term stability		[% of the span]		< ± 0,1; (per 6 months)	
Temperature coefficient zero point		[% of the span / 10 K]		< ± 0,1 (0...80 °C); < ± 0,2 (-40...0 °C / 80...125 °C)	
Temperature coefficient span		[% of the span / 10 K]		< ± 0,1 (0...80 °C); < ± 0,2 (-40...0 °C / 80...125 °C)	
Response times					
Step response time analogue output		[ms]		2	
Operating conditions					
Ambient temperature		[°C]		-40...100	
Storage temperature		[°C]		-40...100	
Protection				IP 67	
Tests / approvals					
EMC		Compliant with ECE R 10, rev. 5		(E1 compliant)	
		DIN EN ISO 13766-1 : 2018		earthworks and construction machines	
		DIN EN ISO 14982 : 2009		agricultural and forestry machines	
		ISO 11452-2		100 V/m	
		ISO 7637-2 : 2011 pulse 1		Test severity III. function state C	
		ISO 7637-2 : 2011 pulse 2b		test severity IV. function state C	
		DIN EN 61326-1			
Shock resistance		DIN EN 60068-2-27		500 g (1 ms)	
Vibration resistance		DIN EN 60068-2-6		20 g (10...2000 Hz)	
MTTF		[years]		715	
UL approval		UL Approval no.		J032	
		File number UL		E174189	
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request			
Mechanical data					
Weight		[g]		67	
Materials		stainless steel (630/1.4542/17-4 PH); stainless steel (316L/1.4404); PPS			
Materials (wetted parts)		stainless steel (630/1.4542/17-4 PH); stainless steel (303/1.4305)			

PT5003



Pressure transmitter

PT-025-SEG14-A-ZVG/VE

Min. pressure cycles	60 million; (at 1.2 times nominal pressure)
Tightening torque [Nm]	25...35; (recommended tightening torque; depends on lubrication, seal and pressure rating)
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)
Process connection sealing	FKM (DIN EN ISO 1179-2)
Restrictor element integrated	yes


Remarks	
Remarks	BFSL = Best Fit Straight Line LS = limit value setting
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x valve plug type A DIN (EN175301-803-A)



Connection




OUT	analogue output
FE	functional earth

Pressure transmitter

PT-025-SEG14-A-ZVG/VE

Diagrams and graphs

characteristic load curve of current output



1: Max. load

2: min. load