
PZ7024

Pressure sensor with LED bar display

PZ-010-RBR14-QFPKG/US/ /E

Article no longer available - archive entry



1 LED bar display
2 programming button

CE

Product characteristics		
Number of inputs and outputs		Number of digital outputs: 2
Measuring range	[bar]	0...10
Process connection		threaded connection G 1/4 internal thread
Application		
Application		for industrial applications
Media		liquids and gases
Medium temperature	[°C]	-25...80
Min. bursting pressure	[bar]	150
Pressure rating	[bar]	50
Type of pressure		relative pressure
Electrical data		
Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 50
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	0.2
Integrated watchdog		yes

PZ7024

Pressure sensor with LED bar display

PZ-010-RBR14-QFPKG/US/ /E

Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2
Outputs		
Total number of outputs		2
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	10
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Measuring range	[bar]	0...10
Set point SP	[bar]	0.5...10
In steps of	[bar]	0.1
Hysteresis	[bar]	0.2
Accuracy / deviations		
Switch point accuracy [% of the final value]		< ± 2,0
Repeatability [% of the final value]		< ± 0,25; (with temperature fluctuations < 10 K)
Temperature drift per 10 K		< ± 0.3
Software / programming		
Adjustment of the switch point		programming button
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 65

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

Mechanical data	
Materials	EPDM/X; FKM; NBR; PBT; PC; PTFE; stainless steel (1.4301 / 304)
Materials (wetted parts)	EPDM/X; ceramics; stainless steel (1.4305 / 303)

PZ7024

Pressure sensor with LED bar display

PZ-010-RBR14-QFPKG/US/ /E

Min. pressure cycles	100 million	
Process connection	threaded connection G 1/4 internal thread	
Displays / operating elements		
Display	switching status	2 x LED, yellow
	measured values	10 x LED, green Resolution 10% of the final value
Remarks		
Pack quantity	1 pcs.	
Electrical connection		

Connector: 1 x M12; coding: A



