

RU-0600-I24/N2

The technical drawing consists of two views of a mechanical component:

- Front View (Left):** A circular cross-section with a diameter of $\varnothing 42$. It features three holes arranged in a triangular pattern with a 120° angle between them. One hole is labeled '1' and another '2'. A fillet with a radius of $R17$ is shown at the bottom left, angled at 30° .
- Side View (Right):** A longitudinal section showing the internal profile. Key dimensions include:
 - Total length: 46^{-1}
 - Distance from left face to first step: 15
 - Distance between steps: 10
 - Thickness of the last step: 4
 - Internal bore diameter: $\varnothing 50^{+0.07}_{-0}$
 - Outer diameter of the main body: $\varnothing 58$
 - Inner diameter of the central bore: $\varnothing 6$
 - Distance from right face to internal feature: $12,5$
 - Small gaps or clearances are dimensioned as 3 and 3 .
 - A feature at the bottom is labeled '3'.

CE

Resolution	600 resolution
Shaft design	solid shaft
Shaft diameter [mm]	6

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	150

Electrical design	HTL
Max. current load per output [mA]	50
Switching frequency [kHz]	300
Type of short-circuit protection	< 60 s
Phase difference A and B [°]	90

Resolution	600 resolution
------------	----------------

Ambient temperature	[°C]	-20...85
Storage temperature	[°C]	-30...100
Protection		IP 64

Shock resistance	100 g (6 ms)
------------------	--------------



Incremental encoder with solid shaft

RU-0600-I24/N2

Vibration resistance	10 g (55...2000 Hz)
----------------------	---------------------

Mechanical data

Dimensions	[mm]	Ø 58 / L = 46
Materials		aluminium
Max. revolution, mechanical	[U/min]	12000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	6
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Fixing flange		synchro-flange

Electrical connection

Cable: 2 m, PUR; radial

brown	A
green	A inverted
grey	B
pink	B inverted
red	0 index
black	0 index inverted
blue	L+ sensor
white	0V sensor
brown/green	L+ (Up)
white/green	0V (Un)
lilac	failure inverted
screen	housing

Diagrams and graphs

Pulse diagram	direction of rotation clockwise (looking at the shaft)
---------------	---