


Flow monitor

SID10ABBFPG/US-100-IPF

Article no longer available - archive entry



- 1 internal thread M18 x 1.5
2 setting pushbuttons



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2
Process connection	M18 x 1,5 internal thread

Application

Media	Liquids; Gases
Medium temperature [°C]	-25...80
Pressure rating [bar]	30

Liquids

Medium temperature [°C]	-25...80
-------------------------	----------

Gases

Medium temperature [°C]	-25...80
-------------------------	----------

Electrical data

Operating voltage [V]	20...36 DC; (to SELV/PELV)
Current consumption [mA]	< 90
Reverse polarity protection	yes
Power-on delay time [s]	15; (optically indicated)

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2
------------------------------	------------------------------

Outputs

Total number of outputs	2
Output signal	switching signal



Flow monitor

SID10ABBFPKG/US-100-IPF

Electrical design	PNP	
Number of digital outputs	2	
Output function	normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC [V]	2.5	
Permanent current rating of switching output DC [mA]	250	
Short-circuit protection	yes	
Type of short-circuit protection	pulsed	
Overload protection	yes	
Measuring/setting range		
Liquids		
Setting range [cm/s]	3...300	
Greatest sensitivity [cm/s]	3...60	
Gases		
Setting range [cm/s]	200...3000	
Greatest sensitivity [cm/s]	200...800	
Accuracy / deviations		
Temperature gradient [K/min]	300	
Response times		
Response time [s]	1...10	
Liquids		
Response time [s]	1...10	
Gases		
Response time [s]	1...10	
Software / programming		
Adjustment of the switch point	pushbutton	
Operating conditions		
Ambient temperature [°C]	-25...80	
Protection	IP 67	
Tests / approvals		
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (55...2000 Hz)
Mechanical data		
Dimensions [mm]	M18 x 1.5	
Thread designation	M18 x 1.5	
Materials	PBT-GF20	
Materials (wetted parts)	stainless steel (1.4404 / 316L); O-ring: FPM 8 x 1,5 gr 80° Shore A	
Process connection	M18 x 1,5 internal thread	
Displays / operating elements		
Display	function	10 x LED, three-colour

SI0102



Flow monitor

SID10ABBFPKG/US-100-IPF

Remarks

Pack quantity

1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection

