
TA2437

Temperature transmitter

TA-100CLER12-A-ZVG/US



Product characteristics		
Number of inputs and outputs		Number of analogue outputs: 1
Measuring range	[°C]	-50...150
Communication interface		IO-Link
Process connection		threaded connection G 1/2
Installation length EL	[mm]	100
Application		
Special feature		Gold-plated contacts
Measuring element		1 x Pt 1000; (to DIN EN 60751, class A)
Media		liquids and gases
Pressure rating	[bar]	160
Note on pressure rating		sensor
		When mounted in adapters the specifications of the adapter data sheet apply.
Electrical data		
Operating voltage	[V]	18...32 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	1
Inputs / outputs		
Number of inputs and outputs		Number of analogue outputs: 1
Outputs		
Total number of outputs		1
Output signal		analogue signal; IO-Link; (configurable)
Number of analogue outputs		1
Analogue current output	[mA]	4...20
Max. load	[Ω]	250; ((18...19 V); 19...32 V: 300 Ω)
Short-circuit protection		yes
Overload protection		yes
Measuring/setting range		
Measuring range	[°C]	-50...150

TA2437

Temperature transmitter

TA-100CLER12-A-ZVG/US

Factory setting			0...100 °C
Resolution			
Resolution of analogue output	[K]		0.04
Accuracy / deviations			
Precision analogue output	[K]		± 0,3 + (± 0,1 % MS)
Temperature coefficient	[% of the span / 10 K]		0,1; (in case of deviation from the reference condition 25 ± 5 °C)
Response times			
Dynamic response T05 / T09	[s]		1 / 3
Interfaces			
Communication interface			IO-Link
Transmission type			COM2 (38,4 kBaud)
IO-Link revision			1.1
Operating conditions			
Ambient temperature	[°C]		-25...80
Storage temperature	[°C]		-40...100
Protection			IP 67; IP 68; IP 69K
Tests / approvals			
EMC		DIN EN 61000-6-2	
Shock resistance		DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance		DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]		230
UL approval		UL Approval no.	K002
Mechanical data			
Weight	[g]		131
Materials			stainless steel (1.4404 / 316L); PEI; FKM
Materials (wetted parts)			stainless steel (1.4404 / 316L); O-ring: FKM
Tightening torque	[Nm]		45
Process connection			threaded connection G 1/2
Probe diameter	[mm]		6
Installation length EL	[mm]		100
Displays / operating elements			
Display		operating status	1 x LED, green
Remarks			
Remarks			MS = set measuring span
Pack quantity			1 pcs.


TA2437

Temperature transmitter

TA-100CLER12-A-ZVG/US

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

