




AS-Interface universal module

UniversalModule 2AO(V) IP65



1 panel for labelling



Application		
Application		field installation
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	140
Reverse polarity protection		yes
Additional voltage supply	[V]	24...30 DC; (AUX)
Additional voltage supply		optional
Max. current consumption from additional supply	[mA]	550; (AUX)
Inputs / outputs		
Number of inputs and outputs		Number of analogue outputs: 2
Inputs		
Precision analogue input	[%]	0,5
Outputs		
Number of analogue outputs		2; (connection of 2-wire or 4-wire actuators)
Analogue voltage output	[V]	0...10
Min. load resistance	[Ω]	3300
Overload protection		yes
Resolution of analogue output		16 (1 bit = 1 mV)
Actuator supply outputs		AS-i / AUX

AC2619



AS-Interface universal module

UniversalModule 2AO(V) IP65

Operating conditions		
Ambient temperature	[°C]	0...70
Storage temperature	[°C]	-25...85
Max. relative air humidity	[%]	90; (non condensing)
Max. height above sea level	[m]	2000
Protection		IP 65
Tests / approvals		
EMC	EN 50295	
MTTF	[years]	145
AS-i classification		
AS-i master profile		M3; M4
AS-i profile		S-7.3.5
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	3.5
Mechanical data		
Weight	[g]	296.5
Type of mounting		AS-i interface to FC-E lower parts
Materials		PBT
Displays / operating elements		
Display	analogue signal	LED, yellow channels AO1...AO2
	operation	LED, green AS-i, AUX
	errors	LED, red
Electrical connection		
Module connection		Flat cables
Remarks		
Pack quantity		1 pcs.
Electrical connection		
cage clamps:		




AS-Interface universal module

UniversalModule 2AO(V) IP65

contact pins to module lower part, FK / FK-E / PG:

Connection



- | | |
|----|----------------------------|
| 1 | O+ actuator supply 2 +24V |
| 2 | V2 analogue output V |
| 3 | O- actuator supply 2 0V |
| 4 | COM 2 analogue output 2 0V |
| 5 | Shield |
| 6 | Shield |
| 7 | O+ actuator supply 1 +24V |
| 8 | V1 analogue output V |
| 9 | O- actuator supply 10V |
| 10 | COM 1 analogue output 1 0V |
| 11 | FE functional earth |
| 12 | FE functional earth |