


Article no longer available - archive entry



1 6 Outputs with PG cable gland

**Electrical data**

Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 240
Reverse polarity protection		yes
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4
------------------------------	-----------------------------

Inputs

Number of digital inputs		4
Sensor supply of the inputs		AS-i / AUX
Power supply	[V]	20...30
Max. total current rating of inputs	[mA]	200
Input current High	[mA]	> 5
Input current Low	[mA]	< 1.5
Switching level high	[V]	> 10
Digital inputs protected against short circuits		yes

Outputs

Electrical design	AS-i
Circuit	PNP

AC9240



AS-Interface module

MODULE ASI PG7/9 4E 200M

Short-circuit proof		yes	
Electrically separated		yes	
Operating conditions			
Ambient temperature		[°C]	-25...80
Protection		IP 68	
Tests / approvals			
EMC		EN 50081-1	
		EN 61000-6-2	
AS-i classification			
AS-i profile		S-0.0	
AS-i I/O configuration		[hex]	0
AS-i ID code		[hex]	0
Mechanical data			
Materials		PA	
Displays / operating elements			
Display		switching status	LED, yellow
		operation	LED, green
Accessories			
Accessories (optional)		PG cable gland: 2 x PG9	
		PG cable gland: 4 x PG7	
Remarks			
Pack quantity		1 pcs.	