


## Fibre optic through-beam sensor

FE-00-M-V-E3/1,5m

Article no longer available - archive entry

Alternative articles: E20492

When selecting an alternative article and accessories please note that technical data may differ!



## Application

Function principle

Through-beam sensor

## Detection zone

Range with fibre-optic amplifier type

OKF; OUF

## OKF

Range of fibre optics

[mm]

108

## OUF

Range of fibre optics

[mm]

108

## Operating conditions

Ambient temperature

[°C]

-20...150

## Mechanical data

Version of sensing head

straight

Sensing head diameter

[mm]

3

Sensing head length

[mm]

10

Total length

[mm]

1500

# E20536



## Fibre optic through-beam sensor

FE-00-M-V-E3/1,5m

|                       |      |                                |
|-----------------------|------|--------------------------------|
| Min. bending radius   | [mm] | 20                             |
| Fibre material        |      | glass                          |
| Fibre head material   |      | stainless steel (1.4305 / 303) |
| Fibre sheath material |      | metal silicone                 |
| Remarks               |      |                                |
| Pack quantity         |      | 1 pcs.                         |