


Fibre optic through-beam sensor

FE-00-M-V-M4/0,3M

Article no longer available - archive entry

Alternative articles: E20505

When selecting an alternative article and accessories please note that technical data may differ!



Application

Function principle	Through-beam sensor
--------------------	---------------------

Detection zone

Range with fibre-optic amplifier type	OKF; OUF
---------------------------------------	----------

OKF

Range of fibre optics [mm]	120
----------------------------	-----

OUF

Range of fibre optics [mm]	120
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-20...150
--------------------------	-----------

Mechanical data

Version of sensing head	straight
Sensing head thread	M4
Sensing head length [mm]	15
Total length [mm]	300

E20726



Fibre optic through-beam sensor

FE-00-M-V-M4/0,3M

Min. bending radius	[mm]	20
Fibre material		glass
Fibre head material		stainless steel (1.4305 / 303)
Fibre sheath material		metal silicone
Remarks		
Pack quantity		1 pcs.