



Retro-reflective sensor

OCP-CPKG/US-100

Article no longer available - archive entry

Alternative articles: O5P500

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available

Product characteristics

Type of light	red light
Housing	rectangular

Application

Special feature	polarisation filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 30
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		PNP
Output function		complementary
Max. voltage drop switching output DC	[V]	2.9
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	1500
Short-circuit protection		yes
Type of short-circuit protection		pulsed

**Retro-reflective sensor**

OCP-CPKG/US-100

Overload protection	yes
---------------------	-----

Detection zone

Range [m]	< 5
Range adjustable	yes
Max. light spot diameter [mm]	130
Light spot dimensions refer to	at maximum range
Polarisation filter available	yes

Operating conditions

Ambient temperature [°C]	-40...60
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2
-----	--------------

Mechanical data

Housing	rectangular
Dimensions [mm]	49 x 15 x 42
Materials	diecast zinc
Lens material	PMMA

Displays / operating elements

Display	switching status	1 x LED, yellow
	function	1 x LED, yellow flashing

Accessories

Items supplied	screwdrivers
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection


Connector: 1 x M12; coding: A



Retro-reflective sensor

OCP-CPKG/US-100

Connection



Diagrams and graphs

excess gain graph

