


KG5069



Capacitive sensor

KG-3080NFPKGS2T



- 1 LED ring
2 programming buttons



Product characteristics

Electrical design	PNP
Output function	normally open / normally closed; (selectable)
Sensing range [mm]	8
Communication interface	IO-Link
Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 77

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 20
Protection class	II
Reverse polarity protection	yes
Measuring principle	capacitive

Outputs

Electrical design	PNP
Output function	normally open / normally closed; (selectable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	10
Short-circuit proof	yes
Overload protection	yes

Detection zone

Sensing range [mm]	8
--------------------	---

Accuracy / deviations

Hysteresis [% of Sr]	1...15
Switch point drift [% of Sr]	-20...20

Interfaces

Communication interface	IO-Link
Transmission type	COM1 (4,8 kBaud)

KG5069



Capacitive sensor

KG-3080NFPKGS2T

IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor	
SIO mode	yes	
Min. process cycle time [ms]	101	
Supported DeviceIDs	Type of operation	DeviceID
	default	387

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 65; IP 67

Tests / approvals

EMC	EN 61000-4-2 ESD	8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
Vibration resistance	EN 60068-2-6 Fc	(10...55 Hz) / 1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz
Shock resistance	EN 60068-2-27 Ea	30 g 6 shocks / 11 ms half-sine (x, y, z)
MTTF [years]	653	

Mechanical data

Weight [g]	97.3
Housing	threaded type
Mounting	non-flush mountable
Dimensions [mm]	M18 x 1 / L = 77
Thread designation	M18 x 1
Materials	housing: PP white; Sealing: TPE-U; pushbuttons: TPE-U

Displays / operating elements

Display	switching status	1 x LED, yellow
Teach function	yes	
Electronic lock	yes	

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

KG5069




Capacitive sensor

KG-3080NFPKGS2T

Electrical connection

Cable: 2 m, PVC, Ø 4.9 mm; 3 x 0.34 mm²

Connection



BK: OUT / IO-Link
Core colours :
BK = black
BN = brown
BU = blue