

# PM2656




## Flush pressure transmitter

PM-2,5-REA01-E-ZVG/US/ /P

Article no longer available - archive entry

Alternative articles: PM1606  
When selecting an alternative article and accessories please note that technical data may differ!



1 Tightening torque 20 Nm



### Product characteristics

|                              |                                                      |                  |                 |               |
|------------------------------|------------------------------------------------------|------------------|-----------------|---------------|
| Number of inputs and outputs | Number of analogue outputs: 1                        |                  |                 |               |
| Measuring range              | -0.13...2.5 bar                                      | -130...2500 mbar | -1.8...36.3 psi | -13...250 kPa |
| Process connection           | threaded connection G 1 external thread sealing cone |                  |                 |               |

### Application

|                         |                                                                       |         |          |
|-------------------------|-----------------------------------------------------------------------|---------|----------|
| Special feature         | Gold-plated contacts                                                  |         |          |
| Application             | flush mountable for the food and beverage industry                    |         |          |
| Media                   | viscous media and liquids with suspended particles; liquids and gases |         |          |
| Medium temperature [°C] | -25...125; (145 max. 1h)                                              |         |          |
| Min. bursting pressure  | 50 bar                                                                | 725 psi | 5000 kPa |
| Pressure rating         | 20 bar                                                                | 290 psi | 2000 kPa |
| Type of pressure        | relative pressure                                                     |         |          |
| No dead space           | yes                                                                   |         |          |



## Flush pressure transmitter

PM-2,5-REA01-E-ZVG/US/ /P

| Electrical data                    |                        |                                                                                                                      |                  |                                    |
|------------------------------------|------------------------|----------------------------------------------------------------------------------------------------------------------|------------------|------------------------------------|
| Operating voltage                  | [V]                    | 14...30 DC                                                                                                           |                  |                                    |
| Min. insulation resistance         | [MΩ]                   | 100; (500 V DC)                                                                                                      |                  |                                    |
| Protection class                   |                        | III                                                                                                                  |                  |                                    |
| Reverse polarity protection        |                        | yes                                                                                                                  |                  |                                    |
| Measuring principle                |                        | hydrostatic                                                                                                          |                  |                                    |
| Inputs / outputs                   |                        |                                                                                                                      |                  |                                    |
| Number of inputs and outputs       |                        | Number of analogue outputs: 1                                                                                        |                  |                                    |
| Outputs                            |                        |                                                                                                                      |                  |                                    |
| Total number of outputs            |                        | 1                                                                                                                    |                  |                                    |
| Output signal                      |                        | analogue signal                                                                                                      |                  |                                    |
| Number of analogue outputs         |                        | 1                                                                                                                    |                  |                                    |
| Analogue current output            | [mA]                   | 4...20                                                                                                               |                  |                                    |
| Max. load                          | [Ω]                    | 550; (Ub = 24 V; (Ub - 13 V) / 20 mA)                                                                                |                  |                                    |
| Overload protection                |                        | yes                                                                                                                  |                  |                                    |
| Measuring/setting range            |                        |                                                                                                                      |                  |                                    |
| Measuring range                    |                        | -0.13...2.5 bar                                                                                                      | -130...2500 mbar | -1.8...36.3 psi      -13...250 kPa |
| Analogue start point               |                        | -0.13...1.88 bar                                                                                                     | -1.8...27.2 psi  | -13...188 kPa                      |
| Analogue end point                 |                        | 0.5...2.5 bar                                                                                                        | 7.3...36.3 psi   | 50...250 kPa                       |
| In steps of                        |                        | 0.01 bar                                                                                                             | 0.1 psi          | 1 kPa                              |
| Factory setting                    |                        |                                                                                                                      | ASP = 0.0 bar    | AEP = 2.50 bar                     |
| Accuracy / deviations              |                        |                                                                                                                      |                  |                                    |
| Repeatability                      | [% of the span]        | < ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)                                                       |                  |                                    |
| Characteristics deviation          | [% of the span]        | < ± 0,6; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1) |                  |                                    |
| Linearity deviation                | [% of the span]        | < ± 0,5; (Turn down 1:1)                                                                                             |                  |                                    |
| Hysteresis deviation               | [% of the span]        | < ± 0,1; (Turn down 1:1)                                                                                             |                  |                                    |
| Long-term stability                | [% of the span]        | < ± 0,1; (Turn down 1:1; per year)                                                                                   |                  |                                    |
| Temperature coefficient zero point | [% of the span / 10 K] | < ± 0,1; (0...80 °C)                                                                                                 |                  |                                    |
| Temperature coefficient span       | [% of the span / 10 K] | < ± 0,2; (0...80 °C)                                                                                                 |                  |                                    |
| Response times                     |                        |                                                                                                                      |                  |                                    |
| Max. response time analogue output | [ms]                   | 3                                                                                                                    |                  |                                    |
| Software / programming             |                        |                                                                                                                      |                  |                                    |
| Parameter setting options          |                        | zero point; span                                                                                                     |                  |                                    |
| Interfaces                         |                        |                                                                                                                      |                  |                                    |
| Communication interface            |                        | EPS                                                                                                                  |                  |                                    |
| Operating conditions               |                        |                                                                                                                      |                  |                                    |
| Ambient temperature                | [°C]                   | -25...80                                                                                                             |                  |                                    |

PM2656



Flush pressure transmitter

PM-2,5-REA01-E-ZVG/US/ /P

|                     |      |           |
|---------------------|------|-----------|
| Storage temperature | [°C] | -40...100 |
| Protection          |      | IP 67     |

Tests / approvals

|                      |                           |                     |
|----------------------|---------------------------|---------------------|
| EMC                  | EN 61000-4-2 ESD          | 4 kV CD / 8 kV AD   |
|                      | EN 61000-4-3 HF radiated  | 10 V/m              |
|                      | EN 61000-4-4 Burst        | 2 kV                |
|                      | EN 61000-4-6 HF conducted | 10 V                |
| Shock resistance     | DIN IEC 68-2-27           | 50 g (11 ms)        |
| Vibration resistance | DIN IEC 68-2-6            | 20 g (10...2000 Hz) |

Mechanical data

|                          |     |                                                                                                           |
|--------------------------|-----|-----------------------------------------------------------------------------------------------------------|
| Weight                   | [g] | 534                                                                                                       |
| Materials                |     | stainless steel (316L/1.4404); PEI; FKM                                                                   |
| Materials (wetted parts) |     | ceramics (99.9 % Al2O3); stainless steel (316L/1.4435);<br>surface characteristics: Ra < 0,4 / Rz 4; PTFE |
| Min. pressure cycles     |     | 100 million                                                                                               |
| Process connection       |     | threaded connection G 1 external thread sealing cone                                                      |

Remarks

|               |                                                                                                   |
|---------------|---------------------------------------------------------------------------------------------------|
| Remarks       | The 3-A qualification is only valid if adapters with 3-A qualification are used for installation. |
| Pack quantity | 1 pcs.                                                                                            |

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

