




Flush pressure sensor with display

PI-025-REB34-MFRKG/US/ IP

Article no longer available - archive entry

Alternative articles: PI2993

When selecting an alternative article and accessories please note that technical data may differ!



- 1 7-segment LED display
- 2 programming button
- 3 diaphragm : PTFE



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	-1...25 bar	-15...363 psi	-0.1...2.5 MPa
Process connection	threaded connection G 3/4 external thread		

Application

Special feature	Gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Installation	freely rotatable housing 350°		
Media	liquid and viscous media		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	200 bar	2900 psi	20 MPa
Pressure rating	100 bar	1450 psi	10 MPa
Type of pressure	relative pressure		
No dead space	yes		

Electrical data

Operating voltage [V]	20...30 DC; ("supply class 2" to cULus)		
Current consumption [mA]	< 60		
Min. insulation resistance [MΩ]	100; (500 V DC)		



Flush pressure sensor with display

PI-025-REB34-MFRKG/US/ IP

Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	0.2
Integrated watchdog	yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
------------------------------	---

Outputs

Total number of outputs	2
Output signal	switching signal; analogue signal; (configurable)
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	< 170
Number of analogue outputs	1
Analogue current output [mA]	4...20; (scalable 1:4)
Max. load [Ω]	(U _b - 10 V) / 20 mA
Analogue voltage output [V]	0...10; (scalable 1:4)
Min. load resistance [Ω]	2000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range

Measuring range	-1...25 bar	-15...363 psi	-0.1...2.5 MPa
Set point SP	-0.8...25 bar	-12...363 psi	-0.08...2.5 MPa
Reset point rP	-0.9...24.9 bar	-13...362 psi	-0.09...2.49 MPa
Analogue start point	-1...18.8 bar	-15...272 psi	-0.1...1.88 MPa
Analogue end point	5.3...25 bar	76...363 psi	0.53...2.5 MPa
In steps of	0.1 bar	1 psi	0.01 MPa

Accuracy / deviations

Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)
Characteristics deviation [% of the span]	< ± 0,6; (Turn down 1:1, linearity, incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1)
Linearity deviation [% of the span]	< ± 0,5; (Turn down 1:1)
Hysteresis deviation [% of the span]	< ± 0,1; (Turn down 1:1)
Long-term stability [% of the span]	< ± 0,1; (Turn down 1:1; per year)
Temperature coefficient zero point [% of the span / 10 K]	< ± 0,15; (0...80 °C)



Flush pressure sensor with display

PI-025-REB34-MFRKG/US/ IP

Temperature coefficient span [% of the span / 10 K]	< ± 0,4; (0...80 °C)
--	----------------------

Response times

Response time [ms]	< 3
Damping process value dAP [s]	0...4
Damping for the analogue output dAA in steps	0 - 0,1 - 0,5 - 2
Max. response time analogue output [ms]	3

Software / programming

Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span
---------------------------	---

Operating conditions

Ambient temperature [°C]	-25...80
Storage temperature [°C]	-40...100
Protection	IP 67

Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

Mechanical data

Materials	stainless steel (316L/1.4404); PBT; PC; PA; EPDM/X; FKM
Materials (wetted parts)	stainless steel (316L/1.4404); PTFE on ceramic substrate; PTFE; FKM
Min. pressure cycles	100 million
Process connection	threaded connection G 3/4 external thread

Displays / operating elements

Display	switching status	2 x LED, red
	function display	7-segment LED display
	measured values	7-segment LED display
Display unit	bar; psi; MPa	

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated







Flush pressure sensor with display

PI-025-REB34-MFRKG/US/ IP

Connection



OUT1
OUT2

switching output
switching output
analogue output