




Flow sensor with integrated backflow prevention

SBU12DF0BPKG/US



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1
Process connection	G 1/2

Application

Application	laser cooling
Media	water
Medium temperature [°C]	0...60
Pressure rating [bar]	20
Pressure rating [MPa]	2

Electrical data

Operating voltage [V]	10...30 DC; (to SELV/PELV)
Current consumption [mA]	< 15
Protection class	III
Reverse polarity protection	yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------



Flow sensor with integrated backflow prevention

SBU12DF0BPKG/US

Outputs		
Total number of outputs		1
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		1
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Short-circuit protection		yes
Overload protection		yes
Measuring/setting range		
Flow range	[l/min]	50
Setting range	[l/min]	1...12
Set point SP	[l/min]	2.5
Note on switch point		± 0,25, fixed
Accuracy / deviations		
Repeatability	[% of the final value]	1
Pressure loss		1 l/min = 0.01 bar; 6 l/min = 0.1 bar; 12 l/min = 0.2 bar; 30 l/min = 0.5 bar; 50 l/min = 1 bar
Hysteresis	[l/min]	0,1...0,2
Response times		
Response time	[s]	< 0.01
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-15...80
Protection		IP 65; IP 67
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	3387
Mechanical data		
Weight	[g]	287.5
Materials		PP; PA; PE
Materials (wetted parts)		stainless steel (316 / 1.4401); stainless steel (1.4301 / 304); PP; PE; PPS; O-ring: FKM
Process connection		G 1/2
Switching cycles mechanical		10 million
Installation position		upright



Flow sensor with integrated backflow prevention

SBU12DF0BPKG/US

Displays / operating elements

Display	switching status	4 x LED, yellow
---------	------------------	-----------------

Remarks


Remarks	Recommendation Use 200 micron filtration
	All data refer to water (20 °C).
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection



colours to DIN EN 60947-5-2
Core colours :
BK = black
BN = brown
BU = blue

SB0506



Flow sensor with integrated backflow prevention

SBU12DF0BPKG/US

Diagrams and graphs

