


SBY457



Flow transmitter with integrated backflow prevention

SBY32HF010KG/US

Please note the changed housing design!



Product characteristics

Measuring range	[l/min]	8...200
Process connection		Rp 1 1/2

Application

Media	Liquids; water; glycol solutions; coolants
Medium temperature	[°C]
Pressure rating	[bar]
Pressure rating	[MPa]

SBY457

Flow transmitter with integrated backflow prevention

SBY32HF010KG/US



Electrical data		
Operating voltage	[V]	18...32 DC; (to SELV/PELV)
Current consumption	[mA]	< 35
Protection class		III
Reverse polarity protection		yes
Outputs		
Output signal		analogue signal
Analogue current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit protection		yes
Overload protection		yes
Measuring/setting range		
Measuring range	[l/min]	8...200
Accuracy / deviations		
Repeatability	[% of the final value]	1
Measuring error	[% of the final value]	± 5
Response times		
Response time	[s]	< 0.01
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-15...80
Protection		IP 65; IP 67
Tests / approvals		
EMC		DIN EN 61000-6-2 DIN EN 61000-6-3
Shock resistance		DIN EN 60068-2-27
Vibration resistance		DIN EN 60068-2-6
MTTF	[years]	778
Mechanical data		
Weight	[g]	2221.05
Materials		brass chemically nickel-plated; PP; stainless steel (316L/1.4404); aluminium anodised; PA
Materials (wetted parts)		stainless steel (316 / 1.4401); brass; brass chemically nickel-plated; PP; PPS; spacer: POM; O-ring: FKM
Process connection		Rp 1 1/2
Switching cycles mechanical		10 million
Remarks		
Remarks		Recommendation Use 200 micron filtration All data refer to water (20 °C).
Notes		Please note the changed housing design!
Pack quantity		1 pcs.

SBY457



Flow transmitter with integrated backflow prevention


SBY32HF010KG/US

Electrical connection

Connector: 1 x M12; coding: A



Connection




colours to DIN EN 60947-5-2

Core colours :

BN = brown
BU = blue
WH = white

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity