




Flow meter with integrated backflow prevention and display

SBN34IQ0FRKG

Please note the changed housing design!



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range	10...600 gph	0.2...10 gpm
Process connection	threaded connection 3/4" NPT	

Application

Special feature	Gold-plated contacts
Application	for industrial applications
Media	Liquids; water; glycol solutions; coolants



Flow meter with integrated backflow prevention and display

SBN34IQ0FRKG

Note on media		oil 1 with viscosity: 10 mm ² /s (104 °F)
		oil 2 with viscosity: 46 mm ² /s (104 °F)
Medium temperature	[°F]	14...212
Pressure rating	[bar]	40
Pressure rating	[MPa]	4
MAWP (for applications according to CRN)	[bar]	40
Electrical data		
Operating voltage	[V]	18...30 DC; (to SELV/PELV)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	< 3
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1
Outputs		
Total number of outputs		2
Output signal		switching signal; analogue signal; frequency signal; IO-Link; (configurable)
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	150; (per output 2 x 200 (...140 °F); 2 x 250 (...104 °F))
Switching cycles (mechanical)		10 million
Number of analogue outputs		1
Analogue current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit protection		yes
Overload protection		yes
Frequency of the output	[Hz]	0...10000
Measuring/setting range		
Measuring range		10...600 gph 0.2...10 gpm
Display range		0...720 gph 0...12 gpm
Resolution		5 gph 0.1 gpm
Set point SP		5...600 gph 0.1...10 gpm
Reset point rP		0...595 gph 0...9.9 gpm
Frequency end point, FEP		40...600 gph 0.67...10 gpm
In steps of		5 gph 0.1 gpm
Frequency at the end point FRP	[Hz]	10...10000
Measuring dynamics		1:50
Temperature monitoring		
Measuring range	[°F]	14...212
Display range	[°F]	-26...252



Flow meter with integrated backflow prevention and display

SBN34IQ0FRKG

Resolution	[°F]	2
Set point SP	[°F]	16...212
In steps of	[°F]	2
Frequency start point, FSP	[°F]	14...172
Frequency end point, FEP	[°F]	54...212
Frequency at the end point FRP	[Hz]	10...10000

Accuracy / deviations

Flow monitoring

Accuracy (in the measuring range)	$\pm (4 \% \text{ MW} + 1 \% \text{ MEW})$; ($Q > 1 \text{ l/min}$; medium and operating temperature: $+71,6 \text{ °F} \pm 4\text{K}$)
Repeatability	$\pm 1 \% \text{ MEW}$

Temperature monitoring

Temperature drift	0,9802 °F / K
Accuracy	[K] 3 K (77 °F; $Q > 1 \text{ l/min}$)

Response times

Flow monitoring

Response time	[s]	0.01
Damping process value dAP	[s]	0...5
Damping for the analogue output dAA	[s]	0...5

Temperature monitoring

Dynamic response T05 / T09	[s]	T09 = 120 ($Q > 1 \text{ l/min}$)
----------------------------	-----	-------------------------------------

Software / programming

Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current output; medium selection; damping for the switching output / analogue output; display can be rotated and switched off; standard unit of measurement; process value colour
---------------------------	--

Interfaces

Communication interface	IO-Link				
Transmission type	COM2 (38,4 kBaud)				
IO-Link revision	1.1				
SDCI standard	IEC 61131-9 CDV				
Profiles	Smart Sensor: Process Data Variable; Device Identification				
SIO mode	yes				
Required master port type	A				
Process data analogue	2				
Process data binary	2				
Min. process cycle time	[ms] 5				
Supported DeviceIDs	<table> <tr> <th>Type of operation</th><th>DeviceID</th></tr> <tr> <td>default</td><td>567</td></tr> </table>	Type of operation	DeviceID	default	567
Type of operation	DeviceID				
default	567				

Operating conditions

Ambient temperature	[°F]	32...140
Note on ambient temperature		medium temperature < 176 °F
		medium temperature < 212 °F: 32...104 °F
Storage temperature	[°F]	5...176



Flow meter with integrated backflow prevention and display

SBN34IQ0FRKG

Protection

IP 65; IP 67

Tests / approvals

EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF [years]		145
UL approval	UL Approval no.	I005
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data

Weight [g]	693
Materials	stainless steel (316L/1.4404); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated
Materials (wetted parts)	stainless steel (316 / 1.4401); stainless steel (316L/1.4404); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM
Process connection	threaded connection 3/4" NPT

Displays / operating elements

Display	Display unit	3 x LED, green
	switching status	2 x LED, yellow
	measured values	alphanumeric display, red/green 4-digit
	programming	alphanumeric display, 4-digit

Remarks

Remarks	Recommendation: use a 200-micron filter.
	All data refer to water (68 °F).
	MW = measured value
	MEW = Final value of the measuring range
Notes	Please note the changed housing design!
Pack quantity	1 pcs.

Electrical connection


Connector: 1 x M12; coding: A; Contacts: gold-plated



Flow meter with integrated backflow prevention and display

SBN34IQ0FRKG

Connection



OUT1:

- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- frequency output volumetric flow quantity monitoring
- frequency output Temperature monitoring
- IO-Link

OUT2:


- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- analogue output volumetric flow quantity monitoring
- analogue output Temperature monitoring
- colours to DIN EN 60947-5-2

Core colours :

- BK = black
- BN = brown
- BU = blue
- WH = white

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity