
SU2020

Ultrasonic flow meter

SUR21XFBFRKG/US



ACS CE PA cULus LISTED IO-Link KTW/W270 Reg31

Product characteristics					
Measuring range		5...1000 l/min	300...60000 l/h	0.058...11.666 m/s	0.3...60 m³/h
Process connection		G 2 DN50 external thread			
Application					
Special feature		Gold-plated contacts			
Media		ultra-pure water; water; hydrous media			
Note on media		hydrous media: for media with >10 % additives, the repeatability is the only available value			
Medium temperature	[°C]	-20...100			
Min. bursting pressure		150 bar	15 MPa		
Pressure rating		100 bar	10 MPa		
Vacuum resistance	[mbar]	-1000			
MAWP (for applications according to CRN)	[bar]	100			
Electrical data					
Operating voltage	[V]	18...32 DC; (to SELV/PELV)			
Current consumption	[mA]	< 75			
Protection class		III			
Reverse polarity protection		yes			
Power-on delay time	[s]	5			
Measuring principle		ultrasonic			

SU2020

Ultrasonic flow meter

SUR21XFBFRKG/US

Inputs					
Inputs		counter reset			
Outputs					
Total number of outputs		2			
Output signal		switching signal; pulse signal; analogue signal; IO-Link; frequency signal; diagnostic signal; totaliser switching signal			
Electrical design		PNP/NPN			
Output function		normally open / normally closed; (parameterisable)			
Max. voltage drop switching output DC	[V]	2			
Permanent current rating of switching output DC	[mA]	100			
Switching frequency DC	[Hz]	0...10000			
Analogue current output	[mA]	4...20			
Max. load	[Ω]	500			
Pulse output		flow rate meter			
Short-circuit protection		yes			
Type of short-circuit protection		pulsed			
Overload protection		yes			
Measuring/setting range					
Measuring range		5...1000 l/min	300...60000 l/h	0.058...11.666 m/s	0.3...60 m³/h
Display range		-1200...1200 l/min	-72000...72000 l/h	-13.999...13.999 m/s	-72...72 m³/h
Resolution		0.1 l/min	1 l/h	0.001 m/s	0.002 m³/h
Set point SP		10.5...1000 l/min	630...60000 l/h	0.122...11.666 m/s	0.63...60 m³/h
Reset point rP		5.3...994.8 l/min	318...59688 l/h	0.062...11.605 m/s	0.318...59.688 m³/h
Analogue start point ASP		-1000...800 l/min	-60000...48000 l/h	-11.666...9.333 m/s	-60...48 m³/h
Analogue end point AEP		-800...1000 l/min	-48000...60000 l/h	-9.333...11.666 m/s	-48...60 m³/h
Low flow cut-off LFC		5...50 l/min	300...3000 l/h	0.058...0.583 m/s	0.3...3 m³/h
Frequency end point, FEP		200.6...1000 l/min	12037...60000 l/h	2.34...11.666 m/s	12.037...60 m³/h
Frequency at the end point FRP	[Hz]	1...10000			
Volumetric flow quantity monitoring					
Pulse length	[s]	0.002...2			
Pulse value		0.1...99990000 l			
Temperature monitoring					
Measuring range	[°C]	-20...100			
Display range	[°C]	-44...124			
Resolution	[°C]	0.1			
Set point SP	[°C]	-19.6...100			
Reset point rP	[°C]	-20...99.6			
Analogue start point	[°C]	-20...76			
Analogue end point	[°C]	4...100			
Frequency start point, FSP	[°C]	-20...76			
Frequency end point, FEP	[°C]	4...100			

SU2020

Ultrasonic flow meter

SUR21XFBFRKG/US

Frequency at the end point FRP	[Hz]	1...10000	
Accuracy / deviations			
Flow monitoring			
Accuracy (in the measuring range)		± (1,0 % MW + 0,5 % MEW)	
Repeatability		± 0,2 % MEW	
Temperature monitoring			
Accuracy	[K]	± 2,5 (Q > 5 % MEW)	
Temperature coefficient [% of the span / 10 K]		0,2	
Response times			
Flow monitoring			
Response time	[s]	< 0.25; (dAP = 0, T09)	
Damping process value dAP	[s]	0...5	
Temperature monitoring			
Dynamic response T05 / T09	[s]	5,7 / 86	
Software / programming			
Diagnostic functions		direction of flow detection; signal quality	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1.3	
SDCI standard		IEC 61131-9: 2013-07	
Profiles		Identification and Diagnosis (0x4000)	
Required master port type		A	
Process data analogue		3	
Process data binary		2	
Min. process cycle time	[ms]	9.6	
IO-Link process data (cyclical)		**function**	**bit length**
		totaliser	32
		Flow monitoring	32
		Temperature monitoring	32
		status	4
		Output 1	1
		Output 2	1
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	1461
Operating conditions			
Ambient temperature	[°C]	-20...60	
Storage temperature	[°C]	-25...80	
Protection		IP 67	
Tests / approvals			
EMC		DIN 61326-1:2021	

SU2020

Ultrasonic flow meter

SUR21XFBFRKG/US

CPA approval		model number	002US
		accuracy class	1,5
Shock resistance		DIN IEC 68-2-27	20 g (11ms)
Vibration resistance		DIN IEC 68-2-6	5 g (10...2000Hz)
MTTF	[years]	160	
UL approval		UL Approval no.	I033
		File number UL	E174189
Pressure Equipment Directive		can be used for group 2 fluids; group 1 fluids on request	

Mechanical data

Weight	[g]	1180	
Type of mounting		inlet pipe length 5xDN; outlet pipe length 1xDN	
Materials		housing: stainless steel (1.4404 / 316L); Display: PFA; Sealing Display: FKM; connector: POKAN	
Materials (wetted parts)		Pipe section: stainless steel (1.4404 / 316L); Process connection sealing: Centellen Flat seal	
Process connection		G 2 DN50 external thread	
Surface characteristics Ra/Rz of the wetted parts		1.25 µm	

Displays / operating elements

Display			colour display 1,44", 128 x 128 pixels
		Switching function	2 x LED, yellow
		diagnosis	1 x LED, three-colour
Display unit		l/min; l/h; m³/h; m/s	

Accessories

Items supplied	Flat seal 2, Centellen
	package insert

Remarks

Remarks	MW = measured value
	MEW = Final value of the measuring range
	pulse and totaliser signal are only available for one of the two outputs
	the accuracy indications are adhered to over the entire application area
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated




SU2020

Ultrasonic flow meter

SUR21XFBFRKG/US


Connection




OUT1/IO-Link:	switching output volumetric flow quantity monitoring switching output Temperature monitoring Pulse output quantity meter frequency output volumetric flow quantity monitoring frequency output Temperature monitoring signal output Preset counter
OUT2/InD:	switching output volumetric flow quantity monitoring switching output Temperature monitoring Pulse output quantity meter analogue output flow analogue output temperature signal output Preset counter input counter reset
colours to DIN EN 60947-5-2	
Core colours	BK= black BN= brown BU= blue WH= white

Diagrams and graphs

Note on pressure loss



derating ambient temperature



1 Ambient temperature

2 Medium temperature