

KNM30NUAFPKG/US-100-DPX



Technical drawing of the LED light fixture showing dimensions and components:

- Overall length: 100
- Distance from mounting bracket to first LED: 90
- Distance between first and second LED: 79
- Distance between second and third LED: 75
- Distance between third and fourth LED: 44
- Distance from fourth LED to end: 15
- Mounting bracket: M12 x 1
- LEDs: 3 LED
- Wrench symbol: 36
- End cap: 5
- End cap thread: M30 x 1,5



電気仕様	PNP
出力機能	ノーマルオープン / ノーマルクローズ, (切替可能)
外装	ねじ切り形
外形寸法 [mm]	M30 x 1.5 / L = 100

特長	金メッキ接点, 自己診断機能
取付	非金属材料の容器越しに検出
媒体	ドライバルク, 液体
媒体温度	-25～80

使用電源電圧範囲	[V]	DC 10～36
消費電流	[mA]	30, (24 V)
保護クラス		II
逆接続保護		有

電気仕様	PNP
出力機能	ノーマルオープン / ノーマルクローズ, (切替可能)
スイッチング出力時のDC電圧降下(最大)	2.5
自己診断機能	有

KN5101



静電容量式近接センサ

KNM30NUAFPKG/US-100-DPX

自己診断機能、自己診断機能 内部電圧降下(最大)	[V]	3.5
診断出力負荷電流	[mA]	10
出力開閉電流 (DC)	[mA]	250
応答周波数 (DC)	[Hz]	5
短絡保護		有
短絡保護機能タイプ		パルス
過負荷保護回路		有

使用環境条件

使用周囲温度	[°C]	-25～80
保護構造		IP 67

試験 / 認証

EMC	EN 60947-5-2
-----	--------------

機械的仕様

外装	ねじ切り形
取付け	埋込み不可
外形寸法	[mm] M30 x 1.5 / L = 100
ねじ規格	M30 x 1.5
材質	真鍮 白銅コーティング, PBT, 塩化ビニール (PVC)

ディスプレイ / パーツ

表示	スイッチング状態	1 x LED, 黄色
	動作	1 x LED, 緑
	機能	1 x LED, 赤

アクセサリ

付属品	ロックナット: 2
-----	-----------

備考

梱包数	1 個
-----	-----

KN5101





静電容量式近接センサ

KNM30NUAFPKG/US-100-DPX

電気接続 - プラグ

コネクタ式: 1 x M12, コーディング: A, コンタクト: 金メッキ



2: 自己診断機能 プログラミング配線