


# EVC964



## Connection cable

VDOGH050MSE0010C05STGH050MSS



Application		
Special feature	Halogen-free; Gold-plated contacts; Screened cable; Drag chain suitability	
Application	CAN bus	
Electrical data		
Operating voltage [V]	32 DC; (wires 4+5: 5 V)	
Max. current load total [A]	4; (wires 4+5: 0,05 A)	
Operating conditions		
Ambient temperature [°C]	-25...80	
Protection	IP 67; IP 68; IP 69K	
Mechanical data		
Weight [g]	1009.25	
Moulded-body material	TPU	
Material nut	brass, nickel-plated	
Sealing material	FKM	
Drag chain suitability	yes	
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s <sup>2</sup>
	bending cycles	> 5 Mio.
	torsional strain	± 180 °/m
Remarks		
Remarks	The CAN bus terminating resistor (120 Ω) is integrated in the M12 connector.	
Pack quantity	1 pcs.	

# EVC964




## Connection cable

VDOGH050MSE0010C05STGH050MSS

### Electrical connection - plug


Connector: 1 x M12, straight; Moulded body: TPU, black; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



### Electrical connection

Cable: 10 m, PUR, Halogen-free, lilac,  $\varnothing$  8.4 mm, shielded; RD / BK: 2 x 0.75 mm<sup>2</sup> (42 x  $\varnothing$  0.15 mm) + WH / BU: 2 x 0.5 mm<sup>2</sup> (19 x  $\varnothing$  0.19 mm) + screen: 1 x 0.75 mm<sup>2</sup> (42 x  $\varnothing$  0.15 mm)

### Connection



### Electrical connection - socket

Connector: 1 x M12, straight; Moulded body: TPU, black; Locking: brass, nickel-plated; Sealing: FKM; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm

